



High Voltage Power Capacitors

REQUEST FOR QUOTATION			
PRODUCT GROUP	HIGH VOLTAGE CAPACITOR		
REQUEST FOR QUOTATION			
REFERENCE FOR INQUIRY			
QUOTATION NUMBER			
TECHNICAL SPECIFICATION			
		REQUESTED	OFFERED
RATED VOLTAGE*	KV		
FREQUENCY*	HZ		
RATED OUTPUT*	KVAR		
CONNECTION	SINGLE PHASE/THREE PHASE		
NUMBER OF BUSHINGS*	1 / 2 / 3		
INSTALLATION*	INDOOR / OUTDOOR		
CAPACITANCE	μF		
ELEMENT FUSE	YES / NO		
DISCHARGE RESISTOR	YES / NO		
STANDARD			
TEMPERATURE CLASS	-...../+.....°C		
INSULATION LEVEL	KV / KVP		
ENCLOSURE			
PROTECTION	IP..		
DIMENSION L X W X H	( MM )		
REPLACEMENT	YES / NO		
IF YES, WHAT TO REPLACE			
DIMENSIONS	L X W X H (MM)		
PRESSURE MONITORING	YES / NO		
* = NO QUOTATION POSSIBLE WITHOUT THIS INFO			
CONDITIONS			
QUANTITY			
DELIVERY	( EX WORKS/FOB/CIF... )		
TERMS OF PAYMENT			
REQUESTED VALIDITY			
REQUESTED DELIVERY			

# Request For Quotation

Vishay ESTA

High Voltage Power Capacitors



<b>REQUEST FOR QUOTATION</b>			
PRODUCT GROUP	HIGH VOLTAGE CAPACITOR BANK		
REQUEST FOR QUOTATION			
REFERENCE FOR INQUIRY			
QUOTATION NUMBER			
<b>TECHNICAL SPECIFICATION</b>			
		<b>REQUESTED</b>	<b>OFFERED</b>
RATED VOLTAGE*	KV		
FREQUENCY*	HZ		
RATED OUTPUT*	MVAR		
INSTALLATION*	INDOOR / OUTDOOR		
CONNECTION*	SINGLE PHASE, STAR, DELTA		
CAPACITANCE	µF		
UNBALANCE PROTECTION	YES / NO		
ELEMENT FUSE	YES / NO		
DISCHARGE RESISTOR	YES / NO		
STANDARD			
TEMPERATURE CLASS	-...../+.....°C		
INSULATION LEVEL	KV / KVP		
ENCLOSURE			
PROTECTION	IP...		
REPLACEMENT	YES / NO		
IF YES, WHAT TO REPLACE			
<b>* = NO QUOTATION POSSIBLE WITHOUT THIS INFO</b>			
CONDITIONS			
QUANTITY			
DELIVERY	( EX WORKS/FOB/CIF... )		
TERMS OF PAYMENT			
REQUESTED VALIDITY			
REQUESTED DELIVERY			