

Resistor Packaging

SMD FILM TAPE AND REEL PACKAGING							
MODEL	SIZE	PACKAGING CODE		DIMENSIONS IN INCHES (mm)			PACKAGING UNIT (Pieces)
		LEAD (Pb)-BEARING	LEAD (Pb)-FREE	REEL SIZE	P	W	
CDHV	2512	TT, ST	ET, FT, NT	7	0.315 (8.00)	0.472 (12.00)	250 min. to 2000 max.
		T5, S5	E5, F5, N5	7	0.315 (8.00)	0.472 (12.00)	500
		T1, S1	E1, F1, N1	7	0.315 (8.00)	0.472 (12.00)	1000
		TF, SF	EF, FF, NF	7	0.315 (8.00)	0.472 (12.00)	2000
CDMV	2512	TT	ET, NT	7	0.315 (8.00)	0.472 (12.00)	250 min. to 2000 max.
		T5	E5, N5	7	0.315 (8.00)	0.472 (12.00)	500
		T1	E1, N1	7	0.315 (8.00)	0.472 (12.00)	1000
		TF	EF, NF	7	0.315 (8.00)	0.472 (12.00)	2000
CRHV	1206, 1210	TT, ST	ET, FT, NT	7	0.157 (4.00)	0.315 (8.00)	250 min. to 4000 max.
		T5, S5	E5, F5, N5	7	0.157 (4.00)	0.315 (8.00)	500
		T1, S1	E1, F1, N1	7	0.157 (4.00)	0.315 (8.00)	1000
		TF, SF	EF, FF, NF	7	0.157 (4.00)	0.315 (8.00)	4000
	2010	TT, ST	ET, FT, NT	7	0.157 (4.00)	0.472 (12.00)	250 min. to 4000 max.
		T5, S5	E5, F5, N5	7	0.157 (4.00)	0.472 (12.00)	500
		T1, S1	E1, F1, N1	7	0.157 (4.00)	0.472 (12.00)	1000
		TF, SF	EF, FF, NF	7	0.157 (4.00)	0.472 (12.00)	4000
	2510, 2512	TT, ST	ET, FT, NT	7	0.315 (8.00)	0.472 (12.00)	250 min. to 2000 max.
		T5, S5	E5, F5, N5	7	0.315 (8.00)	0.472 (12.00)	500
		T1, S1	E1, F1, N1	7	0.315 (8.00)	0.472 (12.00)	1000
		TF, SF	EF, FF, NF	7	0.315 (8.00)	0.472 (12.00)	2000
CRMV	1206, 1210	TT	ET, NT	7	0.157 (4.00)	0.315 (8.00)	250 min. to 4000 max.
		T5	E5, N5	7	0.157 (4.00)	0.315 (8.00)	500
		T1	E1, N1	7	0.157 (4.00)	0.315 (8.00)	1000
		TF	EF, NF	7	0.157 (4.00)	0.315 (8.00)	4000
	2010	TT	ET, NT	7	0.157 (4.00)	0.472 (12.00)	250 min. to 4000 max.
		T5	E5, N5	7	0.157 (4.00)	0.472 (12.00)	500
		T1	E1, N1	7	0.157 (4.00)	0.472 (12.00)	1000
		TF	EF, NF	7	0.157 (4.00)	0.472 (12.00)	4000
	2510, 2512	TT	ET, NT	7	0.315 (8.00)	0.472 (12.00)	250 min. to 2000 max.
		T5	E5, N5	7	0.315 (8.00)	0.472 (12.00)	500
		T1	E1, N1	7	0.315 (8.00)	0.472 (12.00)	1000
		TF	EF, NF	7	0.315 (8.00)	0.472 (12.00)	2000
PSF	2012	TA	EA	13	0.315 (8.00)	0.472 (12.00)	2000
	4527	TA	EA	13	0.472 (12.00)	0.945 (24.00)	1200



SMD FILM TAPE AND REEL PACKAGING (continued)							
MODEL	SIZE	PACKAGING CODE		DIMENSIONS IN INCHES (mm)			PACKAGING UNIT (Pieces)
		LEAD (Pb)-BEARING	LEAD (Pb)-FREE	REEL SIZE	P	W	
RC	0540, 0550, 0575, 1100, 1206, 5100	TT, ST	ET, FT, NT	7	0.157 (4.00)	0.315 (8.00)	250 min. to 4000 max.
		T5, S5	E5, F5, N5	7	0.157 (4.00)	0.315 (8.00)	500
		T1, S1	E1, F1, N1	7	0.157 (4.00)	0.315 (8.00)	1000
		TF, SF	EF, FF, NF	7	0.157 (4.00)	0.315 (8.00)	4000
	5150, 2010, 7225	TT, ST	ET, FT, NT	7	0.157 (4.00)	0.472 (12.00)	250 min. to 4000 max.
		T5, S5	E5, F5, N5	7	0.157 (4.00)	0.472 (12.00)	500
		T1, S1	E1, F1, N1	7	0.157 (4.00)	0.472 (12.00)	1000
		TF, SF	EF, FF, NF	7	0.157 (4.00)	0.472 (12.00)	4000
RCHR	0805, 1005, 1206	TT, ST	ET, FT, NT	7	0.157 (4.00)	0.315 (8.00)	250 min. to 4000 max.
		T5, S5	E5, F5, N5	7	0.157 (4.00)	0.315 (8.00)	500
		T1, S1	E1, F1, N1	7	0.157 (4.00)	0.315 (8.00)	1000
		TF, SF	EF, FF, NF	7	0.157 (4.00)	0.315 (8.00)	4000
RCP	0505, 0603, 1206	TP	EA	7	0.157 (4.00)	0.315 (8.00)	4000
		S3	EB	7	0.157 (4.00)	0.315 (8.00)	1000
		S2	EC	7	0.157 (4.00)	0.315 (8.00)	500
		S6	ED	7	0.157 (4.00)	0.315 (8.00)	300
	2512	TP	EA	7	0.315 (8.00)	0.472 (12.00)	2000
		S3	EB	7	0.315 (8.00)	0.472 (12.00)	1000
		S2	EC	7	0.315 (8.00)	0.472 (12.00)	500
		S6	ED	7	0.315 (8.00)	0.472 (12.00)	300
RCWE	0402	TA	EA	7	0.079 (2.00)	0.315 (8.00)	10 000
	0603, 0805, 0612, 1206, 1210	TA	EA	7	0.157 (4.00)	0.315 (8.00)	5000
	1020, 2010	TA	EA	7	0.157 (4.00)	0.472 (12.00)	4000
	2512	TA	EA	7	0.315 (8.00)	0.472 (12.00)	2000
RCWH	0805	TA	EA	7	0.157 (4.00)	0.315 (8.00)	5000
RCWK	0306	TA	EA	7	0.157 (4.00)	0.315 (8.00)	5000
RCWL	0402	TA	EA	7	0.079 (2.00)	0.315 (8.00)	10 000
	0603, 0805, 1206	TA	EA	7	0.157 (4.00)	0.315 (8.00)	5000
	1210	TA	EA	7	0.157 (4.00)	0.472 (12.00)	5000
	1218, 2010	TA	EA	7	0.157 (4.00)	0.472 (12.00)	4000
	2512	TA	EA	7	0.315 (8.00)	0.472 (12.00)	2000
RCWP	0201	UA	EA	7	0.079 (2.00)	0.315 (8.00)	4000
		UD	EB	7	0.079 (2.00)	0.315 (8.00)	1000
		UC	EC	7	0.079 (2.00)	0.315 (8.00)	500
		UB	ED	7	0.079 (2.00)	0.315 (8.00)	300
	0302, 0402	TP	EA	7	0.079 (2.00)	0.315 (8.00)	4000
		S3	EB	7	0.079 (2.00)	0.315 (8.00)	1000
		S2	EC	7	0.079 (2.00)	0.315 (8.00)	500
		S6	ED	7	0.079 (2.00)	0.315 (8.00)	300
	0502, 0540, 0550, 0575, 0603, 1100, 1206, 1210, 5100	TP	EA	7	0.157 (4.00)	0.315 (8.00)	4000
		S3	EB	7	0.157 (4.00)	0.315 (8.00)	1000
		S2	EC	7	0.157 (4.00)	0.315 (8.00)	500
		S6	ED	7	0.157 (4.00)	0.315 (8.00)	300
	2010, 5150, 7225	TP	EA	7	0.157 (4.00)	0.472 (12.00)	4000
		S3	EB	7	0.157 (4.00)	0.472 (12.00)	1000
		S2	EC	7	0.157 (4.00)	0.472 (12.00)	500
		S6	ED	7	0.157 (4.00)	0.472 (12.00)	300
2512	TP	EA	7	0.315 (8.00)	0.472 (12.00)	2000	
	S3	EB	7	0.315 (8.00)	0.472 (12.00)	1000	
	S2	EC	7	0.315 (8.00)	0.472 (12.00)	500	
	S6	ED	7	0.315 (8.00)	0.472 (12.00)	300	



SMD FILM TAPE AND REEL PACKAGING (continued)							
MODEL	SIZE	PACKAGING CODE		DIMENSIONS IN INCHES (mm)			PACKAGING UNIT (Pieces)
		LEAD (Pb)-BEARING	LEAD (Pb)-FREE	REEL SIZE	P	W	
RCWPM (Military M/D55342) and RCWPM Jumper (M32159)	0302, 0402	TP, TN	n/a	7	0.079 (2.00)	0.315 (8.00)	4000
		S3, SV	n/a	7	0.079 (2.00)	0.315 (8.00)	1000
		S2, SU	n/a	7	0.079 (2.00)	0.315 (8.00)	500
		S6, ST	n/a	7	0.079 (2.00)	0.315 (8.00)	300
		UL	n/a	7	0.079 (2.00)	0.315 (8.00)	300 min. to 4000 max.
	0502, 0550, 0575, 0603, 1100, 1206, 5100	TP, TN	n/a	7	0.157 (4.00)	0.315 (8.00)	4000
		S3, SV	n/a	7	0.157 (4.00)	0.315 (8.00)	1000
		S2, SU	n/a	7	0.157 (4.00)	0.315 (8.00)	500
		S6, ST	n/a	7	0.157 (4.00)	0.315 (8.00)	300
		UL	n/a	7	0.157 (4.00)	0.315 (8.00)	300 min. to 4000 max.
	2010, 5150, 7225	TP, TN	n/a	7	0.157 (4.00)	0.472 (12.00)	4000
		S3, SV	n/a	7	0.157 (4.00)	0.472 (12.00)	1000
		S2, SU	n/a	7	0.157 (4.00)	0.472 (12.00)	500
		S6, ST	n/a	7	0.157 (4.00)	0.472 (12.00)	300
		UL	n/a	7	0.157 (4.00)	0.472 (12.00)	300 min. to 4000 max.
	2512	TP, TN	n/a	7	0.315 (8.00)	0.472 (12.00)	2000
		S3, SV	n/a	7	0.315 (8.00)	0.472 (12.00)	1000
		S2, SU	n/a	7	0.315 (8.00)	0.472 (12.00)	500
		S6, ST	n/a	7	0.315 (8.00)	0.472 (12.00)	300
		UL	n/a	7	0.315 (8.00)	0.472 (12.00)	300 min. to 2000 max.

SMD FILM TRAY PACKAGING				
MODEL	SIZE	PACKAGING CODE		PACKAGING UNIT ⁽¹⁾ (PIECES)
		LEAD (Pb)-BEARING	LEAD (Pb)-FREE	
CDHV	2512	TW, SW	EW, FW, NW	25
CDMV	2512	TW	EW, NW	25
CRHV	1206, 1210	TW, SW	EW, FW, NW	100
	2010	TW, SW	EW, FW, NW	50
	2510, 2512	TW, SW	EW, FW, NW	25
CRMV	1206, 1210	TW	EW, NW	100
	2010	TW	EW, NW	50
	2510, 2512	TW	EW, NW	25
RC	0540, 0550, 0575, 1100, 1206, 5100	TW, SW	EW, FW, NW	100
	5150, 2010, 7225	TW, SW	EW, FW, NW	50
RCHR	0805, 1005, 1206	TW, SW	EW, FW, NW	100
RCP	0550, 0603, 1206	WB	ET	100
	2512	WB	ET	25
RCWP	0302, 0402, 0502, 0540, 0550, 0575, 0603, 1100, 1206, 1210, 5100	WB	ET	100
	2010, 5150, 7225	WB	ET	50
	2512	WB	ET	25
RCWPM (Military M/D55342) and RCWPM Jumper (M32159)	0302, 0402, 0502, 0550, 0603, 0575, 1100, 1206, 5100	WB, WA	n/a	100
		WL	n/a	25 min. to 100 max.
	2010, 5150, 7225	WB, WA	n/a	50
		WL	n/a	25 min. to 50 max.
	2512	WB, WA	n/a	25
		WL	n/a	25

Note

⁽¹⁾ Units are packaged in 2" by 2" waffle trays



SMD FILM BAG PACKAGING				
MODEL	SIZE	PACKAGING CODE		PACKAGING UNIT ⁽²⁾ (PIECES)
		LEAD (Pb)-BEARING	LEAD (Pb)-FREE	
CDHV	2512	TB, SB	EB, FB, NB	250 min.
CDMV	2512	TB	EB, NB	250 min.
CRHV	1206, 1210, 2010, 2510, 2512	TB, SB	EB, FB, NB	250 min.
CRMV	1206, 1210, 2010, 2510, 2512	TB	EB, NB	250 min.
PSF	2012, 4527	BA	EK	100
RC	0540, 0550, 0575, 1100, 1206, 5100, 5150, 2010, 7225	TB, SB	EB, FB, NB	250 min.
RCHR	0575, 1005, 1206	TB, SB	EB, FB, NB	250 min.

Note

⁽¹⁾ Units are packaged in poly bags