



Carrier Tape for WCSP 3 x 4

Version -1



Version -2, Version -3



VERSION	A_0	B_0	K_0	CENTER HOLE
-1	1.55 ± 0.05	1.96 ± 0.05	0.75 ± 0.05	
-2	1.55 ± 0.05	1.96 ± 0.05	0.75 ± 0.05	0.20 ± 0.05
-3	1.55 ± 0.05	1.96 ± 0.05	0.75 ± 0.05	0.40 ± 0.05

Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1 cm in 1 m actually.
3. Material: black conductive polycarbonate / polystyrene.
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
5. All sizes in mm unless specified.
6. Surface resistivity -10^5 max. Ω/sq .

ECN: E15-1156-Rev. D, 25-May-15
 DWG: 93-5316-X