



ENVIRONMENTAL AND PACKAGE TESTING DATA FOR MICRO FOOT® 4 X 4 AND 4 X 3					
Stress	Sample Size	Device Hr./Cyc	Condition	Total Fails	Fail Percentage
Pressure Pot	110	10,560	121°, 15 PSIG	0	0.00
Temp Cycle	850	456,260	-65°C-150°C	0	0.00