




PowerPAK® SC-75 and Thin PowerPAK SC-75



VERSION	A ₀	B ₀	K ₀
- 1	1.8 ± 0.05	1.8 ± 0.05	0.88 ± 0.05

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2.
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
- (3) Material: PS + C or PC.
- (4) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- (5) All sizes in mm unless specified.
- (6) Vishay part number must be labeled at all reels of cover and carrier tape.
- (7) Surface resistivity: 10⁴ to 10¹¹ Ω.

QUANTITY PER REEL	
T1	3000

ECN: C15-0527-Rev. D, 25-May-15
 DWG: 93-5241-X