


PowerPAK[®] SC-70 and Thin PowerPAK SC-70



VERSION	A_0	B_0	K_0
- 1	2.25 ± 0.05	2.25 ± 0.05	1 ± 0.05

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 .
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
- (3) Material: PS + C or PC.
- (4) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- (5) All sizes in mm unless specified.
- (6) Vishay part number must be labeled at all reels of cover and carrier tape.
- (7) Surface resistivity: $1 \times 10^4 \Omega$ to $1 \times 10^{11} \Omega$.

QUANTITY PER REEL	
T1	3000
T4	3000
T5	3000

ECN: C18-1412-Rev. H, 05-Nov-2018 DWG: 93-5240-X
