



**ENVIRONMENTAL AND PACKAGE TESTING DATA FOR PolarPAK™**

<b>Stress</b>	<b>Sample Size</b>	<b>Device Hr./Cyc</b>	<b>Condition</b>	<b>Total Fails</b>	<b>Fail Percentage</b>
HAST	330	33,000	130°C, 85%RH	0	0.00
Pressure Pot	330	31,680	121°, 15 PSIG	0	0.00
Solder DUNK	330	990	260°C, 10 SEC	0	0.00
Temp Cycle	330	330,000	-65°C-150°C	0	0.00