



<b>ENVIRONMENTAL AND PACKAGE TESTING DATA FOR PowerPAK® 1212-8S</b>					
<b>STRESS</b>	<b>SAMPLE SIZE</b>	<b>DEVICE HR./CYC</b>	<b>CONDITION</b>	<b>TOTAL FAILS</b>	<b>FAIL PERCENTAGE</b>
BOND INT	120	60 000	200 °C + N2	0	0
HAST	656	65 600	130 °C, 85 % RH	0	0
Pressure Pot	736	70 848	121°, 15 PSIG	0	0
Temp. Cycle	656	634 000	-55 °C to 150 °C	0	0