






















Package Dimensions for ESD -, Zener -, Small Signal Switching -, and Schottky Diodes

PACKAGE		PAGE
CLP0603-2L		3
CLP1006-2L		4
CLP1406-2L		5
CLP1608-2L		6
CLP0603-2M		7
CLP1007-5L		8
DFN1006-2A		9
DFN1006-2B		10
DFN1110-3A		11
LLP1006-2L		12
LLP1006-2M		13

PACKAGE		PAGE
LLP1006-3L		14
LLP1010-5L		15
LLP1010-6M		16
LLP1713-7L		17
LLP1713-9L		18
LLP2513-13L		19
LLP3313-17L		20
LLP75-4L		21
LLP75-6L		22
LLP75-7L		23






PACKAGE		PAGE
SOD-123		24
SOD-323		25
SOD-523		26
SOT-23		27
SOT-323		28
SOT-363		29
SMF (DO-219AB)		30
SMA (DO-214AC)		31
MELF DO-213AB (Plastic)		32
MELE DO-213AB (Glass)		33
MicroMELF		33

PACKAGE		PAGE
MicroSMF (DO-219-AC)		35
MiniMELE (SOD-80)		36
QuadroMELE (SOD-80)		37
DO-35 (DO-204AH)		37
DO-35_2		37
DO-41 (DO-204AL) (glass)		38
SOD-57		38
SOD-64		39




CLP0603-2L PACKAGE DIMENSIONS in millimeters (inches)



	mm			mils		
	min.	nom.	max.	min.	nom.	max.
A	0.25	0.28	0.30	9.84	11.02	11.81
A1	0.01	0.01	0.02	0.39	0.39	0.79
A2	0.24	0.27	0.28	9.54	10.63	11.02
b	0.22	0.25	0.28	8.66	9.84	11.02
D	0.27	0.30	0.33	10.62	11.81	12.99
E	0.57	0.60	0.63	22.44	23.62	24.80
e		0.40			15.75	
e1		0.25			9.84	
L	0.12	0.15	0.18	4.72	5.91	7.09

foot print recommendation:





Document no.:S8-V-3906.04-023 (4)
Created - Date: 22. Nov. 2010
Rev.9 - Date: 15. Feb. 2017

[< back](#)




CLP1006-2L PACKAGE DIMENSIONS in millimeters (inches)



	min.	max.
A	0.25	0.29
A1		0.02
b	0.48	0.53
D	0.59	0.63
E	0.99	1.03
e	0.65	
L2	0.23	0.28
L3	0.23	0.28

foot print recommendation:




Document no.:S8-V-3906.04-039 (4)
 Created - Date: 02. April 2015
 Rev.2 - Date: 03. Feb. 2016

[< back](#)




CLP1406-2L PACKAGE DIMENSIONS in millimeters (inches)



	min.	max.
A	0.25	0.29
A1		0.02
b	0.46	0.50
D	0.59	0.63
E	1.39	1.43
e	0.77	
L2	0.23	0.27
L3	0.75	0.79

foot print recommendation:




Document no.:S8-V-3906.04-045 (4)
Created - Date: 22. Jan. 2016

[< back](#)




CLP1608-2L PACKAGE DIMENSIONS in millimeters (inches)



		A	A1	b	D	E	L	L2	L3
mm	min.	0.25		0.58	1.55	0.75	1.42	0.85	0.25
	max.	0.29	0.02	0.65	1.65	0.85	1.52	0.93	0.33

foot print recommendation:





Document no.:S8-V-3906.04-033 (4)
 Created - Date: 10. Feb. 2014
 Rev.4 - Date: 02. July. 2019

[< back](#)




CLP0603-2M PACKAGE DIMENSIONS in millimeters (inches)



	min.	max.
A	0.25	0.29
A1		0.02
b2	0.19	0.24
b3	0.17	0.22
D	0.29	0.33
E	0.59	0.63
e	0.40	
L2	0.10	0.15
L3	0.10	0.15

foot print recommendation:



Document no.:S8-V-3906.04-038 (4)


Created - Date: 01. April 2015

Rev.3 - Date: 15. Feb. 2017

[< back](#)




CLP1007-5L PACKAGE DIMENSIONS in millimeters



	Millimeters	
	min.	max.
A	0.25	0.29
A1	-	0.02
b	0.13	0.17
D	0.68	0.73
E	0.98	1.03
e	0.35	
L	0.23	0.27
Radius	0.075	
d	0.03	

foot print recommendation:





Document no.: S8-V-3906.04-041 (4)

Created - Date: 11-Aug-2015


Rev. 1 - Date: 30-Jul-2019

[< back](#)

DFN1006-2A PACKAGE DIMENSIONS in millimeters (inches)



foot print recommendation:



Document no.:S8-V-3906.04-059 (4)

Created - Date: 11.July.2018


Rev.1 - Date: 15.January.2019

[< back](#)




DFN1006-2B PACKAGE DIMENSIONS in millimeters (inches)

Package = Chip Dimension in mm



Footprint recommendation




Document no.: S8-V-3906.04-059 (4)
Created - Date: 11-Jul-2018
Rev.5 - Date: 17-Sep-2021

23191


[< back](#)



DFN1110-3A PACKAGE DIMENSIONS in millimeters (inches)



foot print recommendation:




Document no.: S8-V-3906.04-062 (4)
Package name: DFN1110-3A
Created - Date: 04-Apr-2019


[< back](#)



LLP1006-2L PACKAGE DIMENSIONS in millimeters (inches)



Foot print recommendation:




Pad Design Patented:
(©US 9.018.537 B2)

Document no.: S8-V-3906.04-005 (4)
Created - Date: 13.July.2007
Rev. 7 - Date: 11.May 2016
20812


[< back](#)



LLP1006-2M PACKAGE DIMENSIONS in millimeters (inches)



Foot print recommendation:




Pad Design Patented:
(©) US 9.018.537 B2

Document no.: S8-V-3906.04-005 (4)
Created - Date: 15.Jun 2009
Rev. 7 - Date: 11.May 2016
20812

[< back](#)




LLP1006-3L PACKAGE DIMENSIONS in millimeters (inches)



	Millimeters	
	Min.	Max.
D	0.95	1.05
E	0.55	0.65
A	0.33	0.40
A1	0	0.05
b	0.2	
L	0.20	0.30
e	0.6	

Foot print recommendation:




Document no.:S8-V-3906.04-044 (4)
Created - Date: 03. Sep. 2015

[< back](#)



LLP1010-5L PACKAGE DIMENSIONS in millimeters (inches)




Document no.:S8-V-3906.04-007 (4)
 Created - Date: 15. April. 2008
 Rev. 3 - Date: 11. May. 2016

[< back](#)



LLP1010-6M PACKAGE DIMENSIONS in millimeters





Document no.:S8-V-3906.04-004 (4)
 Created - Date: 17.July 2007
 Rev. 5 - Date: 11.May 2016

[< back](#)



LLP1713-7L PACKAGE DIMENSIONS in millimeters (inches)




Document no.:S8-V-3906.04-008 (4)
 Created - Date: 15. April 2008
 Rev. 3 - Date: 10.Okt.2019


[< back](#)



LLP1713-9L PACKAGE DIMENSIONS in millimeters (inches)



Foot print recommendation:



Document no.:S8-V-3906.04-001 (4)


Created - Date: 28. August 2006

Rev. 1 - Date: 27. May 2008


[< back](#)



LLP2513-13L PACKAGE DIMENSIONS in millimeters (inches)




Foot print recommendation:




Document no.:S8-V-3906.04-002 (4)
 Created - Date: 28. August 2006
 Rev. 1 - Date: 27. May 2008

[< back](#)

LLP3313-17L PACKAGE DIMENSIONS in millimeters (inches)



Foot print recommendation:




Document no.:S8-V-3906.04-003 (4)
 Created - Date: 28. August 2006
 Rev. 1 - Date: 27. May 2008


[< back](#)



LLP75-4L PACKAGE DIMENSIONS in millimeters (inches)



Foot print recommendation:




Document no.:S8-V-3906.02-015 (4)
 Created - Date: 04. September 2007
 Rev. 2 - Date: 09. Sep. 2008

[< back](#)



LLP75-6L PACKAGE DIMENSIONS in millimeters (inches)




Document no.:S8-V-3906.02-010 (4)
 Created - Date: 04. May 2005
 Rev. 4 - Date: 21. March 2006

[< back](#)



SOD-123 PACKAGE DIMENSIONS in millimeters (inches)




Rev. 4 - Date: 24. Sep. 2009
Document no.: S8-V-3910.01-001 (4)


[< back](#)



SOD-323 PACKAGE DIMENSIONS in millimeters (inches)



Footprint recommendation:




Document no.: S8-V-3910.02-001 (4)
Created - Date: 24.August.2004
Rev. 6 - Date: 23.Sept.2016

[< back](#)



SOD-523 PACKAGE DIMENSIONS in millimeters (inches)






Document no.: S8-V-3880.02-003 (4)
Create Date: 04-Apr-2017
Rev. 3 Date: 27-May-2019


[< back](#)



SOT-23 PACKAGE DIMENSIONS in millimeters (inches)






Foot print recommendation:






SOT-323 PACKAGE DIMENSIONS in millimeters (inches)



foot print recommendation:





Document no.: 6.541-5040.02-4
Rev. 1 - Date: 06. April 2010


[< back](#)



SOT-363 PACKAGE DIMENSIONS in millimeters (inches)



foot print recommendation:




Document no.: S8-V-3855.02-002 (4)

Created - Date: 23.June.2017

[< back](#)




SMF (DO-219AB) PACKAGE DIMENSIONS in millimeters (inches)



foot print recommendation:

Reflow soldering



Document no.: S8-V-3915.01-001 (4)


Created - Date: 15. February 2005

Rev. 5 - Date: 09. Oct. 2017

[< back](#)



SMA (DO-214AC) PACKAGE DIMENSIONS in millimeters (inches)




Document no.: S8-V-3848.01-003 (4)
Created - Date: 18. February 1997
Rev. 8 - Date: 10. November 2006

[< back](#)




MELF DO-213AB (PLASTIC) PACKAGE DIMENSIONS in millimeters (inches)




1st Band denotes type and positive end (cathode)

foot print recommendation:






MELF DO-213AB (GLASS) PACKAGE DIMENSIONS in millimeters (inches)



* The gap between plug and glass can be either on cathode or anode side

Foot print recommendation:





Document no.:S8-V-3453.02-001 (4)
Rev. 3 - Date: 07 June 2006

[< back](#)





MicromELF PACKAGE DIMENSIONS in millimeters (inches)



* The gap between plug and glass can be either on cathode or anode side

Foot print recommendation:




Created - Date: 26.July.1996
 Rev. 13 - Date: 07.June.2006
 Document no.:6.560-5007.01-4
 96 12072


[< back](#)




MicroSMF (DO-219AC) PACKAGE DIMENSIONS in millimeters



foot print recommendation
for wave soldering:



foot print recommendation
for reflow soldering:




Document no.:S8-V-3910.03-001 (4)
Created - Date: 02.Dec.2010
Rev. 5 - Date: 06.May. 2014

[< back](#)




MiniMELF (SOD-80) PACKAGE DIMENSIONS in millimeters (inches)



* The gap between plug and glass can be either on cathode or anode side

Foot print recommendation:




Document no.:6.560-5005.01-4
Rev. 8 - Date: 07.June.2006


[< back](#)



QuadroMELF (SOD-80) PACKAGE DIMENSIONS in millimeters (inches)



* The gap between plug and glass can be either on cathode or anode side




Created - Date: 03.November.2003
Rev. 11 - Date: 07.June 2006
Document no.:6.560-5006.01-4

[< back](#)



DO-35 (DO-204AH) PACKAGE DIMENSIONS in millimeters (inches)




Document no.: SB-V-3906.04-031(4)
Rev. 6 - Date: 19. December 2011

[< back](#)

DO-35_02 PACKAGE DIMENSIONS in millimeters (inches)


only for 1N4148 from Tak Cheong (non-automotive part)



Document no.: 6.560-5004.12-4
Created - Date: 17. March 2008

[< back](#)

DO-41 (DO-204AL) (GLASS) PACKAGE DIMENSIONS in millimeters (inches)




Document no.: 6.561-5001.02-4
Rev. 3 - Date: 09 - February 2005

[< back](#)




SOD-57 PACKAGE DIMENSIONS in millimeters (inches)



Rev. 3 - Date: 09.February 2005
Document no.:6.563-5006.3-4

[< back](#)

SOD-64 PACKAGE DIMENSIONS in millimeters (inches)



Rev. 3 - Date: 09.February 2005
Document no.:6.563-5006.4-4

[< back](#)