

Optocoupler

 CERTIFICATE OF PRODUCT CERTIFICATION	
CERTIFICATE NO.: CQC12001080773	Valid from: Jan.16,2023 Valid until: Jan.15,2028
NAME AND REGISTERED ADDRESS OF THE APPLICANT	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia
NAME AND LOCATION OF THE FACTORY	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia
PRODUCT NAME, MODEL AND SPECIFICATION	Optocouplers VOL617A-#****T, VOL618A-#****T, TCLT101#-****T, TCLT100#-****T, VOL616FA-#****T (Note : The # denote as CTR, it can be A-Z or 0-9 or blank. The "xxxx" are denote as package option forming , VDE partial discharged test or customer code, it can be A-Z or 0-9 or blank, T representing Tape & Reel) Reinforced Insulation, DTI > 0.4mm, External Creepage Distance>8.0mm, pass thermal cycling test. Suitable for installation altitude below 5000M.
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB 4943.1-2022
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection
<p>This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022. Date of original issued: Sep.20,2012 The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.</p>	
<p>The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn</p>	
	<p>SIGNATURE: </p>  <p>CHINA QUALITY CERTIFICATION CENTRE</p> 
<p>http://www.cqc.com.cn Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China Tel: +86 10 83886666</p>	
<p>c 0544748</p>	



产品认证证书

证书编号: CQC12001080773

发证日期: 2023年01月16日

有效期至: 2028年01月15日

委托人名称 威旭半导体马来西亚有限公司
及注册地址 No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

制造商名称 威旭半导体马来西亚有限公司
及注册地址 No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

生产企业名称 威旭半导体马来西亚有限公司
及生产地址 No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

产品名称和系列、规格、型号 光电耦合器
 VOL617A-#****T、VOL618A-#****T、TCLT101#-****T、TCLT100#-****T、VOL616FA-#****T
 (注: 型号中的变量解释如下: “#”表示 CTR 等级代码, 可能是字母 A-Z 或者数字 0-9 或空白的组合; “****”表示 VDE 局部放电或者封装形式或客户的代号, 可能是字母 A-Z 或者数字 0-9 或空白的组合。T 表示表示包装方式, 可以是编带和卷轴, 如是料管 T 为空白。) 加强绝缘; 适用于海拔 5000 米及以下; 外部爬电距离 > 8.0mm; 内部绝缘穿透距离 ≥ 0.4mm; 通过热循环测试

产品标准和技术要求 GB 4943.1-2022

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
 本证书为变更证书, 证书首次颁发日期: 2012 年 09 月 20 日
 证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发: 谢肇煦



中国质量认证中心



http://www.cqc.com.cn

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C 0544748