

# Optocoupler



## PRODUCT CERTIFICATE

No.: CQC13001091529

### NAME AND ADDRESS OF THE APPLICANT

Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka Malaysia

### NAME AND ADDRESS OF THE MANUFACTURER

Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka Malaysia

### NAME AND ADDRESS OF THE FACTORY

Vishay Semiconductor Malaysia Sdn Bhd (V002589)  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka Malaysia

### NAME, MODEL AND SPECIFICATION

Opto Couplers

VOW137-xxxx, VOW137-xxxxT, VOW2601-xxxx, VOW2601-xxxxT, VOW2611-xxxx, VOW2611-xxxxT, VOW2201-xxxx, VOW2201-xxxxT, VOW2211-xxxx, VOW2211-xxxxT, VOW2202-xxxx, VOW2202-xxxxT, VOW2212-xxxx, VOW2212-xxxxT (注: 型号中的变量“x”仅代表封装形式和VDE局部放电的代号, 可以是空白, 字母A-Z或者数字1-9的组合) 加强绝缘, 绝缘穿透距离≥0.4mm, 外部爬电距离>10.6mm, 内部爬电距离>7.2mm, 适用于海拔5000米及以下

### THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB4943.1-2011

### CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2012.

Date of issue: Apr.28,2013

Date of expiry: Apr.28,2017

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President: \_\_\_\_\_

Wang Kejiao



## CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China  
<http://www.cqc.com.cn>

C 0045121



# 产品认证证书

证书编号: CQC13001091529

### 申请人名称及地址

威旭半导体马来西亚有限公司  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

### 制造商名称及地址

威旭半导体马来西亚有限公司  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

### 生产企业名称及地址

威旭半导体马来西亚有限公司 (V002589)  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

### 产品名称和系列、规格、型号

光电耦合器

VOW137-xxxx, VOW137-xxxxT, VOW2601-xxxx, VOW2601-xxxxT, VOW2611-xxxx, VOW2611-xxxxT, VOW2201-xxxx, VOW2201-xxxxT, VOW2211-xxxx, VOW2211-xxxxT, VOW2202-xxxx, VOW2202-xxxxT, VOW2212-xxxx, VOW2212-xxxxT (注: 型号中的变量“x”仅代表封装形式和VDE局部放电的代号, 可以是空白, 字母A-Z或者数字1-9的组合) 加强绝缘, 绝缘穿透距离 > 0.4mm, 外部爬电距离 > 10.6mm, 内部爬电距离 > 7.2mm, 适用于海拔5000米及以下

### 产品标准和技术要求

GB4943.1-2011

### 认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471543-2012认证规则的要求, 特发此证。

发证日期: 2013年04月28日      有效期至: 2017年04月28日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路188号9区100070

http://www.cqc.com.cn

C 0045121