



フルハイブリッド (HEVs) 用主要部品





電気モータードライブ (DC/AC)

<p>CERAMIC CAPACITORS</p> <p>High Operating Temperature, Automotive Grade Leaded MLCC Capacitors</p> <p>HOTcap® K...H, A...R, K...R</p> <ul style="list-style-type: none"> • High-reliability MLCC insert with wet build process • High operating temperature (up to 175 °C for K...H and up to 160 °C for A...R and K...R), rated voltages: 50 V, 100 V, 200 V 	<p>RESISTORS</p> <p>High-Voltage Thin Film Flat Chip Resistors, Up to 1 kV Operating Voltage, Range = 121 kΩ to 3.01 MΩ</p> <p>TNPV1210 e3</p> <ul style="list-style-type: none"> • 0.1 %, 0.5 %, and 1 % tolerances • Excellent stability $\Delta R/R \leq 0.05\% \text{ after } 1000 \text{ h at } 70^\circ\text{C}$ 	<p>RECTIFIERS</p> <p>600 V, 30 A Hyperfast Rectifiers</p> <p>VS-ETH3006SHM3</p> <ul style="list-style-type: none"> • TO-263AB (D²PAK) power package optimized for fast battery charging systems and main inverter applications up to 20 kW
<p>RESISTORS</p> <p>Surface-Mount Molded Dividers, High-Voltage</p> <p>CDMx</p> <ul style="list-style-type: none"> • High voltage up to 3000 V, sulfur-resistant • Automotive compliant terminations, wide range of resistance values and ratios <p>*Preliminary</p>	<p>NON-LINEAR RESISTORS</p> <p>NTC Thermistors, Low Thermal Gradient Lug Sensors</p> <p>NTCALUG02A</p> <ul style="list-style-type: none"> • Low thermal gradient surface temperature sensors • High insulation voltage 	<p>INDUCTORS</p> <p>EMI Filters with Flat Copper Wire as SMD or Leaded Up to 260 A</p> <p>Customized EMI Filters</p> <ul style="list-style-type: none"> • Customized solutions for 48 V applications, low DCR, high current
<p>MODULES</p> <p>Trench FS IGBT Modules</p> <p>VS-GC30C065TB</p> <ul style="list-style-type: none"> • Optimized for use with FRED Pt® Gen 4 ultrafast diodes • Low collector-to-emitter voltages, extremely low conduction losses 	<p>FILM CAPACITORS</p> <p>High-Performance DC-Link Capacitors for Automotive Traction Applications (EV/HEV)</p> <p>MKP1849</p> <ul style="list-style-type: none"> • High voltage, high capacitance, high ripple current • Customized upon request 	<p>FILM CAPACITORS</p> <p>Metallized Polypropylene DC-Link Film Capacitors, 450 V_{DC} to 1200 V_{DC}</p> <p>MKP1848</p> <ul style="list-style-type: none"> • OBC and HEV inverter DC link • High ripple current, capacitance up to 400 µF