



<b>REPLACEMENT SERIES TABLE</b>				
<b>WITHDRAWN SERIES</b>		<b>DESIGN</b>	<b>REMARK</b>	<b>REPLACEMENT SERIES</b>
<b>ORDERING CODE</b>	<b>FORMER PART NUMBER</b>			
-	2222 054 .....	Snap-in	General purpose, 85 °C	056/057 PSM-SI
-	2222 055 .....	Snap-in	General purpose, 85 °C	056/057 PSM-SI
-	2222 086 .....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	2222 087 .....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	2222 088 .....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	2222 089 .....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	2222 111 .....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	2222 112 .....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	2222 114 .....	Screw terminal	Long life, 85 °C	106 PED-ST
-	2222 115 .....	Screw terminal	Long life, 85 °C	101/102 PHR-ST
-	2222 154 .....	Screw terminal	Long life, 85 °C	101/102 PHR-ST
-	2222 155 .....	Screw terminal	Long life, 85 °C	101/102 PHR-ST
-	2222 166 .....	4 terminal snap-in	Long life, 85 °C	Contact sales
-	2222 167 .....	4 terminal snap-in	Long life, 85 °C	095 PLL-4TSI 096 PLL-4TSI
-	2222 168 .....	4 terminal snap-in	Long life, 105 °C	Contact sales
-	2222 169 .....	4 terminal snap-in	Long life, 105 °C	Contact sales
-	3148.....	Screw terminal	High ripple ≤ 75 V, 105 °C	Contact sales
-	3173.....	Screw terminal	Long life, 85 °C	101/102 PHR-ST
-	3186.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	3188.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	3191.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	3198.....	Screw terminal	General purpose, 105 °C	104 PHL-ST
-	3199.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
-	3500.....	Screw terminal	Motor start	No replacement
MALTEYE.....	EYE.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
MALTEYM.....	EYM.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
MALTEYP.....	EYP.....	Screw terminal	General purpose, 85 °C	101/102 PHR-ST
MALIEYS.....	EYS.....	Snap-in	General purpose ≤ 100 V, 105 °C	EYH
MALIEYS.....	EYS.....	Snap-in	General purpose > 100 V, 85 °C	093 PMG-SI