MMB 0207 - Professional Sample Kit



Vishay Beyschlag

Sample Kit Professional Thin Film MELF Resistors MMB 0207-50 1 %



Files contain lengths of blister tape, each holding 20 resistors. The kit contains every value of the E12-series. Parts are sorted in the ascending order of its resistance value and appropriately marked.

FEATURES

- Approved according to EN 140401-803
- AEC-Q200 qualified
- Advanced metal film technology
- Excellent overall stability: exceeds class 0.25
- Intrinsic sulfur resistance
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912






COMPLIANT HALOGEN FREE GREEN (5-2008)

SPECIFICATIONS	
Laboratory kit	LMB 12/1
Resistor type	MMB 0207-50 1 %
Temperature coefficient	± 50 ppm/K
Tolerance	± 1 %
Resistance range/E-series	1 Ω to 10 MΩ/every value of E12 $^{(1)}$
Number of resistance values	80
Resistors per value/total	20/1600
Number of pages/files	8/1

Notes

 $^{(1)}\,$ Above 1 $M\Omega$ every second value of E12



Note

• The product can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

The products are specified by the underlying standard product's datasheet "Professional Thin Film MELF Resistors" in its most current edition at <u>www.vishay.com/doc?28713</u>