
























<b>SOLID TANTALUM CHIP CAPACITORS - SURFACE MOUNT</b>										
MODEL	CECC MIL SPEC/ TYPE	OUTLINE DRAWING	CAPACITANCE RANGE (μF)	WORKING VOLTAGES (WVDC)	8 mm TAPE	12 mm TAPE	16 mm TAPE	24 mm TAPE	BLISTER PACK	PAGE
292D	-		1.0 - 47	3 - 20	P, R	-	-	-	-	35
298D	-		1.0 - 220	4 - 25	M, P	-	-	-	-	38
293D 793DX CTC3 CTC4 793DE	- CECC 30801-005 CECC 30801-009 CECC 30801-011 CECC 30801-801		0.10 - 680	4 - 50	A, B, P	C, D, E	-	-	-	41
593D	-		0.47 - 680	4 - 50	A, B	C, D, E	-	-	-	48
TR3	-		0.47 - 680	4 - 50	A, B	C, D, E	-	-	-	53
893D	-		1.0 - 220	6.3 - 50	-	C, D, E	-	-	-	60
TH3	-		0.35 - 100	10 - 50	A, B	C, D, E	-	-	-	63
595D	-		0.10 - 1500	4 - 50	T, A, S	B, C, D, G, H, M, R	-	-	-	78
594D	-		1.0 - 1500	4 - 50	-	B, C, D, R	-	-	-	85
592D	-		1.0 - 3300	4 - 35	A	B, C, D, R	-	X	-	89
591D	-		1.0 - 1000	4 - 35	A	B, C, D, R	-	-	-	97
572D	-		2.2 - 220	4 - 35	P, Q, S, A	B, T	-	-	-	104
597D	-		22 - 1500	4 - 50	-	V	E, R, F	-	-	107

# Quick Reference

Vishay Sprague

Solid Tantalum Chip Capacitors  
TANTAMOUNT® Conformal Coated,  
Maximum CV



SOLID TANTALUM CHIP CAPACITORS - SURFACE MOUNT										
195D	-		0.10 - 330	2 - 50	C, S, V	R, X, Y, Z	-	-	-	110
195D	-		0.10 - 100	2 - 50	A	B, D, E, F, G, H	-	-	-	110
CC/EC	MIL-PRF-55365/4		0.10 - 220	4 - 50	A	B, C, D, E, F	G, H	-	-	120
695D	-		0.10 - 270	4 - 50	A	B, D, E, R, G	H	-	-	125
194D	CECC 30801-001		0.10 - 150	4 - 50	A	B, D, E, F	G, H	-	Y	130
T83	-		0.1 - 330	4 - 50	A, B	C, D, E	-	-	-	144
T95	-		0.1 - 680	4 - 50		B, C, D, R, S, V, X, Y, Z	-	-	-	149
CWR06	MIL-PRF-55365/4		0.10 - 100	4 - 50	A	B, C, D, E, F	G, H	-	-	154
CWR11	MIL-C-55365/8		0.10 - 100	4 - 50	A, B	D	-	-	-	157
CWR16	MIL-PRF-55365/13		0.33 - 330	4 - 35	A	B, C, D, E, F	G, H	-	-	78D