


## CASE OUTLINE FOR THIN PPAK SC75 SINGLE



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.525	0.60	0.65	0.0206	0.024	0.026
A1	0	-	0.05	0	-	0.002
b	0.18	0.25	0.33	0.007	0.010	0.013
C	0.15	0.20	0.25	0.006	0.008	0.0010
D	1.53	1.60	1.70	0.060	0.063	0.067
D1	0.57	0.67	0.77	0.022	0.026	0.030
D2	0.10	0.20	0.30	0.004	0.008	0.012
E	1.53	1.60	1.70	0.060	0.063	0.067
E1	1.00	1.10	1.20	0.039	0.043	0.047
E2	0.20	0.25	0.30	0.008	0.010	0.012
E3	0.32	0.37	0.42	0.013	0.015	0.017
e	0.65 BSC			0.020 BSC		
K	0.180 typ.			0.007 typ.		
K1	0.275 typ.			0.011 typ.		
K2	0.200 typ.			0.008 typ.		
K3	0.255 typ.			0.010 typ.		
K4	0.300 typ.			0.012 typ.		
L	0.15	0.25	0.35	0.006	0.010	0.014
ECN: C11-0404-Rev. A, 11-Apr-11						
DWG: 5999						

**Note**

- All dimensions are in millimeter
- Package outline exclusive of mold flash and metal burr
- Package outline inclusive of plating