



ENVIRONMENTAL AND PACKAGE TESTING DATA FOR MICRO FOOT®					
STRESS	SAMPLE SIZE	DEVICE HR./CYC	CONDITION	TOTAL FAILS	FAIL PERCENTAGE
HAST	2805	280 500	130 °C, 85 % RH	0	0.00
Pressure Pot	1900	182 400	121°, 15 PSIG	0	0.00
Temp. Cycle	2645	2 471 250	- 65 °C to 150 °C	0	0.00