


## PowerPAK® SC-70 AND THIN PowerPAK SC-70



### Notes

1. 10 sprocket hole pitch cumulative tolerance  $\pm 0.2$ .
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
3. Material: PS + C or PC.
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
5. All sizes in mm unless specified.
6. Vishay part number must be labeled at all reels of cover and carrier tape.
7. Surface resistivity -  $10^5$  max.  $\Omega/\text{sq}$ .

QUANTITY PER REEL	
T1	3000
T4	3000
ECN: C12-0449-Rev. D, 21-May-12	
DWG: 93-5240-X	