



ENVIRONMENTAL AND PACKAGE TESTING DATA FOR PowerPAK® 2 x 5					
STRESS	SAMPLE SIZE	DEVICE HR./CYC	CONDITION	TOTAL FAILS	FAIL PERCENTAGE
HAST	100	10 000	130 °C, 85 % RH	0	0.00
Pressure Pot	551	52 896	121°, 15 PSIG	0	0.00
Solder DUNK	80	240	260 °C, 10 s	0	0.00
Solderability	80	120	883 M2003	0	0.00
Temp. Cycle	629	443 750	- 65 °C to 150 °C	0	0.00