


TO252-4L CASE OUTLINE



DIM.	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	2.22	2.38	0.087	0.094
A1	0.95	1.05	0.037	0.041
B1	3.35 BSE		0.132 BSE	
B2	1.74 BSE		0.069 BSE	
b	0.64	0.79	0.025	0.031
b1	0.8	0.86	0.031	0.034
C	0.49	0.53	0.019	0.021
C1	0.508 REF		0.020 REF	
C2	0.495	0.53	0.0195	0.0209
C3	0.509	0.564	0.020	0.0222
D	6.00	6.20	0.236	0.244
D1	5.415	5.515	0.213	0.217

DIM.	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
E	6.40	6.60	0.252	0.260
E1	4.90	5.00	0.193	0.197
E2	5.23	5.43	0.206	0.214
F	0.77 BSC		0.030 BSC	
G	2.65 BSC		0.104 BSC	
H	9.60	10.20	0.378	0.402
L	1.1 REF		0.043 REF	
L1	1.4	1.65	0.055	0.065
L2	0.65	0.95	0.026	0.037
L3	0.01	0.127	0.0004	0.0050
e	1.27 BSC		0.050 BSC	
θ	0°	8°	0°	8°

ECN: T09-0309-Rev. C, 11-May-09
 DWG: 5956