



产品认证证书

证书编号: CQC05001012316

申请人名称及地址

威世电子(惠州)有限公司
广东省惠州市惠阳区淡水镇人民四路46号

制造商名称及地址

威世电子有限公司
Geheimrat-Rosenthal-strasse 100, 95100 Selb 德国

生产企业名称及地址

威世电子(惠州)有限公司(V003957)
广东省惠州市惠阳区淡水镇人民四路46号

产品名称和系列、规格、型号

抑制电源电磁干扰用固定电容器

VY2 X1: 440VAC Y2: 300VAC 100K-103M, AY2 X1: 440VAC Y2: 300VAC 100K-103M, 电容量范围为 10-10000pF, 允许偏差: K: $\pm 10\%$, M: $\pm 20\%$, 气候类别为 40/125/21, 阻燃等级为 C 级

产品标准和技术要求

IEC60384-14:2013+AMD1:2016

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471112-2015 认证规则的要求, 特发此证。

发证日期: 2019 年 03 月 11 日

本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2005 年 03 月 08 日

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>

C 0141156



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC05001012316

NAME AND ADDRESS OF THE APPLICANT

Vishay Components (Huizhou) Co., Ltd.
46 Renmin 4 road, Danshui town, Huiyang District, Huizhou City, Guangdong

NAME AND ADDRESS OF THE MANUFACTURER

VISHAY Electronic GmbH
Geheimrat-Rosenthal-strasse 100,95100 Selb

NAME AND ADDRESS OF THE FACTORY

Vishay Components (Huizhou) Co., Ltd. (V003957)
46 Renmin 4 road, Danshui town, Huiyang District, Huizhou City, Guangdong

PRODUCT NAME, MODEL AND SPECIFICATION

Fixed capacitors for electromagnetic interference suppression and connection to the supply mains

VY2 X1: 440VAC Y2: 300VAC 100K-103M, AY2 X1: 440VAC Y2: 300VAC 100K-103M, 电容量范围为 10-10000pF, 允许偏差: K: ±10%、M: ±20%, 气候类别为 40/125/21, 阻燃等级为 C 级

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

IEC60384-14:2013+AMD1:2016

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471112-2015 .

Valid from: Mar.11,2019

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body.

Date of original issued: Mar.08,2005

President: _____



Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0141156