



PRODUCT CERTIFICATE

No.: CQC07001021279

NAME AND ADDRESS OF THE APPLICANT

VISHAY CAPACITORS BELGIUM NV
Kwadestraat 151a, bus 12, 8800 Roeselare,Belgium

NAME AND ADDRESS OF THE MANUFACTURER

VISHAY CAPACITORS BELGIUM NV
Kwadestraat 151a, bus 12, 8800 Roeselare,Belgium

NAME AND ADDRESS OF THE FACTORY

Vishay Components India Private Limite (V008338)
Loni-Kahlbor, Near Pune, PUNE 412201, INDIA

NAME, MODEL AND SPECIFICATION

Fixed capacitors for electromagnetic interference suppression and connection to the supply mains
338 2 310V~ X2, 1nF~4.7μF 055/110/56/B

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T6346.14-2015

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection


This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471115-2016.

Date of issue: Oct.08,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Sep.21,2007

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President: 
Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0089660