



The DNA of tech.

Product Overview

Function	Blocking Voltage V _{DRM} (V)	Static d _v /d _t (V/μs)	Package		Part Number
Zero Crossing	600	1.5		DIP-6	VO3062, VO3063
		5			VO4156 (300 mA output current)
		10			IL410 (low I _{FT} , 300 mA output current)
		10			IL4116 (low I _{FT} , 300 mA output current)
		20			VOT410A (coming soon) (low I _{FT} , low V _{TM} , 300 mA output current)
	800	1		DIP-4	VOT8024Ax
		1		DIP-6	VOT8025Ax (high isolation distance on output)
		1			VOT8026Ax
		1		SOP-4	VOT8024AM
		5		DIP-6	VO4158 (300 mA output current)
		10			IL4108 (low I _{FT} , 300 mA output current)
		10			IL4118 (low I _{FT} , 300 mA output current)
		20			
Non-Zero Crossing / Random Phase	400	1		DIP-6	VO302x
	600	0.5		SOP-4	VOM160
		1.5			VOM3052, VOM3053
		1.5		DIP-6	VO3052, VO3053
		5			VO4256 (300 mA output current)
		10			IL420 (low I _{FT} , 300 mA output current)
		10			IL4216 (low I _{FT} , 300 mA output current)
		20			
		800	1		SOP-4
	1			DIP-4	VOT8121Ax
	1			DIP-6	VOT8125Ax (high isolation distance on output)
	1				VOT8123Ax
	5			DIP-6	VO4258 (300 mA output current)
	10				IL4208 (low I _{FT} , 300 mA output current)
	10				IL4218 (low I _{FT} , 300 mA output current)
	20				
Special Function	600	0.6		DIP-8	VO2223B (1 A integrated power TRIAC)