



The DNA of tech.

Product Overview

Output Current (A)	Min. Noise Immunity dV/dt (V/μs)	Supply Voltage (V)	Max. Propagation Delay (μs)	Package		Part Number
2.5	35 000	15 to 30	0.5		DIP-8 / SMD-8	VOD3120A
3			0.2		Stretched SO-6	VOFD341A
4			0.2		Stretched SO-6	VOFD343A
0.5	25 000	15 to 32	0.4		DIP-8 / SMD-8	VO3150
2.5			0.5		DIP-8 / SMD-8	VO3120
2.5			0.5		WDIP-8 / WSMD-8	VOW3120