



The DNA of tech.

高速光耦

概览

输入类型	输出类型	速率	封装		隔离	产品名称
模拟	模拟集电极开路 / 漏极开路	100 kBd		SOIC-8	4 mm	SFH6319
				DIP-8	7/8 mm	6N139
				SOIC-8	4 mm	SFH6316
						SFH6343 (30 kV/μs 高抗扰度)
		1 MBd		SOP-4	5 mm	VOMHA43A (车规版, 即将发布)
				SOP-5	5 mm	VOM453
				DIP-8	7/8 mm	SFH6345 (30 kV/μs 高抗扰度)
				WDIP-8	10 mm	VOW136 (1414 V _{IORM} 高隔离电)
		10 MBd		SOIC-8	4 mm	VOIH060A
						VOIH063A (双通道)
				DIP-8	7/8 mm	VOH260A
						VOH263A (双通道)
				WDIP-8	10 mm	VOWH260A (1414 V _{IORM} 高隔离电压)
	Analog Schmitt-Trigger	1 MBd		DIP-6	7 mm	VOH1016A (0.7 mA 低输入电流)
	Digital CMOS	10 MBd		DIP-8	7 mm	VOH61A (即将发布)
Digital	Digital CMOS	25 MBd		SOIC-8	4 mm	VOIH72A (2 ns 脉宽失真)