



The DNA of tech.™




CAPABILITIES AND CUSTOM OPTIONS

ACMKP - POWER ELECTRONIC CAPACITORS

Main Application	Advantage
Sine filter in traction and industrial applications	• High reliability and long lifetime
	• High RMS current rating
	• Internal tear-off fuse
Filter capacitor within a 2-phase or 3-phase system, either in a delta or star connection	• Self-healing technology
	• Low losses at high frequencies



SPECIALTY DEVICES

Design Advantage	Application	Series
Low inductance	Traction	HDMKP 
Robust design, vibration and shock resistant	Traction, industrial	ACMKP rectangular 
High impulse current rating, low inductance	Static converters for transportation, heavy haul locomotives, HVDC transmission	DCMKP rectangular 

CUSTOM OPTIONS

Capabilities
Connections - M6 or M10 bolts, faston
Form - width and height
Electrical parameters
Threaded stud (bottom of container) can be removed