




Carrier Tape for PowerPAK® SO-10LR



Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm
- (2) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole
- (3) A_0 and B_0 are measured on a plane at a distance "R" above the bottom of the pocket
- (4) Material: PS + C

DIMENSIONS	
A_0	5.50 ± 0.10
B_0	7.90 ± 0.10
K_0	1.95 ± 0.10
K_1	1.65 ± 0.10
ECN: C23-0339-Rev. A, 03-Apr-2023 DWG: 93-5358-X	