




Case Outline for PowerPAIR® 6 x 5 FS



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.70	0.75	0.80	0.028	0.030	0.031
A1	0.00	-	0.05	0.000	-	0.002
A2	0.20 ref.			0.008 ref.		
b	0.45	0.50	0.55	0.018	0.020	0.022
D	5.90	6.00	6.10	0.232	0.236	0.240
D1	3.00	3.10	3.20	0.118	0.122	0.126
D2	4.21	4.31	4.41	0.166	0.170	0.174
D3	4.21	4.31	4.41	0.166	0.170	0.174
E	4.90	5.00	5.10	0.193	0.197	0.201
E1	1.76	1.86	1.96	0.069	0.073	0.077
E2	1.66	1.76	1.86	0.065	0.069	0.073
e	1.27 BSC			0.050 BSC		
e1	3.81 BSC			0.150 BSC		
K	0.53 ref.			0.021 ref.		
K1	0.46 ref.			0.018 ref.		
K2	0.40 ref.			0.016 ref.		
K3	0.35 ref.			0.014 ref.		
K4	0.35 ref.			0.014 ref.		
K5	0.35 ref.			0.014 ref.		
K6	0.71 ref.			0.028 ref.		
K7	0.50 ref.			0.020 ref.		
K8	0.35 ref.			0.014 ref.		
L	0.38	0.48	0.58	0.015	0.019	0.023
L1	1.30	1.40	1.50	0.051	0.055	0.059

ECN: T21-0422-Rev. A, 06-Dec-2021
DWG: 6096