




SC-89-L (SOT-666) Carrier Tape



Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually
- (3) Pocket position relative to sprocket hole measured
- (4) Material: PS and C
- (5) All dimension in millimeter unless specified
- (6) Vishay part number must be labeled at all reels of carrier tape
- (7) Surface resistivity: $10^4 \Omega$ to $10^{11} \Omega$

QUANTITY PER REEL	
T1	3000
ECN: C20-0599-Rev. G, 25-May-2020 DWG: 93-5232-X	