




TO-252 (DPAK) REVERSE LEAD (T4 METHOD)



NOTES:

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 .
2. Camber not to exceed 1 mm in 100 mm.
3. Material: Static dissipative black polystyrene.
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
5. All sizes in inches unless specified.

QUANTITY PER REEL	
T4	2500
ECN: S-41135—Rev. F, 19-Jul-04 DWG: 90-2369-x	