


## PowerPAK® SC75-6L (Power IC only)



SECTION A - A

$\text{Ao} = 1.90$   
 $\text{Bo} = 1.90$   
 $\text{Ko} = 1.00$

NOTES:

1. 10 sprocket hole pitch cumulative tolerance  $\pm 0.2$  mm
2. Camber in compliance with EIA 481
3. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole

ECN T-06273-Rev. A, 12-Jun-06  
 DWG: 93-5250-X