



ENVIRONMENTAL AND PACKAGE TESTING DATA FOR THIN POWERPAK® 1212-8					
STRESS	SAMPLE SIZE	DEVICE HR./CYC	CONDITION	TOTAL FAILS	FAIL PERCENTAGE
HAST	164	16 400	130 °C, 85 % RH	0	0.00
Pressure Pot	164	15 744	121°, 15 PSIG	0	0.00
Temp. Cycle	164	164 000	- 65 °C to 150 °C	0	0.00