


Carrier Tape for PowerPAK® 5 x 9



Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm
2. Camber not to exceed 15 mm in 1000 mm
3. Material: black conductive polystyrene
4. All dimensions are in millimeters (unless otherwise specified)
5. K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier
6. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole
7. Surface resistivity: $10^{-4} \Omega$ to $10^{-11} \Omega$

ECN: C19-0309-Rev. B, 02-Apr-2019
DWG: 93-5341-X