


Carrier Tape for MLPA6C



VERSION	A ₀	B ₀	K ₀
- 1	6.9 ± 0.1	11 ± 0.1	3.3 ± 0.1

Notes

- All sizes in mm unless specified
- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2
- (2) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole
- (3) A₀ and B₀ are measured on a plane at a distance "R" above the bottom of the pocket
- (4) Material: PS + C
- (5) Refer: T114855BT REV0

ECN: T23-0019-Rev. C, 16-Jan-2023
 DWG: 93-5348-X