


Carrier Tape for Stack 5 x 5 0.5P 32L



Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm
2. Camber not to exceed 1 mm in 100 mm
3. Static dissipative tri-laminate polystyrene (PS) - black
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole
5. A_0 and B_0 are measured on a plane at a distance R above the bottom of the pocket
6. All sizes in mm unless specified

Version	A_0	B_0	K_0
-1	5.30 ± 0.05	5.30 ± 0.05	1.25 ± 0.10
E20-0085-Rev. A, 16-Mar-2020 DWG: 93-5351-X			