

# Optocoupler



## 产品认证证书

证书编号: CQC14001106301

发证日期: 2023年01月16日

有效期至: 2028年01月15日

**委托人名称** 威旭半导体马来西亚有限公司  
**及注册地址** No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

**制造商名称** 威旭半导体马来西亚有限公司  
**及注册地址** No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

**生产企业名称** 威旭半导体马来西亚有限公司  
**及生产地址** No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

**产品名称和系列、规格、型号** 光电耦合器  
 TCMT110#-\*\*\*\*T; TCMT111#-\*\*\*\*T; TCMT1600-\*\*\*\*T; TCMT1600T3-\*\*\*\*T;  
 TCMT4100-\*\*\*\*T; TCMT4100T0-\*\*\*\*T; TCMT4106-\*\*\*\*T; TCMT4600-\*\*\*\*T;  
 TCMT4600T0-\*\*\*\*T; TCMT4606-\*\*\*\*T; TCMD1000-\*\*\*\*T; TCMD4000-\*\*\*\*T;  
 VOS615B-#\*\*\*\*T, VOS617B-#\*\*\*\*T; VOS618B-#\*\*\*\*T; VOS627B-#\*\*\*\*T; VO628B#-\*\*\*\*T  
 注: 型号中的变量“#”表示 CTR 等级代码, 可能是字母 A-Z 或者数字 0-9 或空白的组合;  
 “\*\*\*\*”表示 VDE 局部放电或是客户的代号, 可能是字母 A-Z 或者数字 0-9 或空白的组合。T 表示包装方式, 可以是编带和卷轴或空白。加强绝缘, 绝缘厚度≥0.4mm, 外部爬电距离≥5.0mm, 通过热循环测试, 适用于海拔 2000 米及以下

**产品标准和技术要求** GB 4943.1-2022

**认证模式** 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。  
 本证书为变更证书, 证书首次颁发日期: 2014 年 04 月 01 日  
 证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 ( www.cnca.gov.cn ) 查验证书信息



签发: 谢肇煦



中国质量认证中心



http://www.cqc.com.cn

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C 0544751

 <b>CERTIFICATE OF PRODUCT CERTIFICATION</b>	
<b>CERTIFICATE NO.:</b> CQC14001106301	<b>Valid from:</b> Jan.16,2023 <b>Valid until:</b> Jan.15,2028
<b>NAME AND REGISTERED ADDRESS OF THE APPLICANT</b>	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia
<b>NAME AND REGISTERED ADDRESS OF THE MANUFACTURER</b>	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia
<b>NAME AND LOCATION OF THE FACTORY</b>	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia
<b>PRODUCT NAME, MODEL AND SPECIFICATION</b>	Optocoupler TCMT110#-****; TCMT111#-****; TCMT1600-****; TCMT1600T3-****; TCMT4100-****; TCMT4100T0-****; TCMT4106-****; TCMT4600-****; TCMT4600T0-****; TCMT4606-****; TCMD1000-****; TCMD4000-****; VOS615B-****; VOS617B-****; VOS618B-****; VOS627B-****; VOG28B#-**** Remarks: The # denotes as CTR, it can be blank or numbers between 0 and 9. The **** denotes as VDE partial discharged or customer codes. It can be characters between A and Z or numbers 0 to 9 or blank. The T represents Tape and Reel or blank. reinforced insulation, distance through insulation≥0.4mm, external creepage distance≥5.0mm, thermal cycling test passed, altitude up to 2000m
<b>THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS</b>	GB 4943.1-2022
<b>TYPE OF CERTIFICATION SCHEMES</b>	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection
<p>This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022. Date of original issued: Apr.01,2014 The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.</p>	
<p>The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn</p>	
	<p><b>SIGNATURE:</b> </p>
	<p><b>CHINA QUALITY CERTIFICATION CENTRE</b></p> 
<p>http://www.cqc.com.cn      Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China      Tel: +86 10 83886666</p>	
<p><b>C 0544751</b></p>	