

Optocoupler



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC23001409207

Valid from: Oct.26,2023

Valid until:Oct.25,2028

NAME AND REGISTERED ADDRESS OF THE APPLICANT	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka, Malaysia
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	Vishay Philippines Inc. Food Terminal Inc. - Special Economic Zone, Bagsakan Road, FTI, Taguig City, Metro Manila
NAME AND LOCATION OF THE FACTORY	Automated Technology Philippines Inc. Light Industry and Science Park of the Philippines, Hologram St, Cabuyao, Laguna, Philippines
PRODUCT NAME, MODEL AND SPECIFICATION	Opto Coupler CNY64(A, B), CNY65(A, B), CNY66(A, B), CNY64(AYST, ABST, AGRST), CNY65(AYST, ABST, AGRST), CNY651(AGR, AYST, AGRST) Reinforced insulation, external creepage > 9.0mm, DTI≥3.0mm, passed thermal cycling test. Altitude Installation up to 5000m
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB 4943.1-2022
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



CHINA QUALITY CERTIFICATION CENTRE

http://www.cqc.com.cn

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666



产品认证证书

证书编号: CQC23001409207

发证日期: 2023年10月26日
有效期至: 2028年10月25日

委托人名称 及注册地址	威旭半导体马来西亚有限公司 No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚
制造商名称 及注册地址	Vishay Philippines Inc. Food Terminal Inc. - Special Economic Zone, Bagsakan Road, FTI, Taguig City, Metro Manila
生产企业名称 及生产地址	Automated Technology Philippines Inc. Light Industry and Science Park of the Philippines, Hologram St, Cabuyao, Laguna, Philippines
产品名称和系列、 规格、型号	光电耦合器 CNY64(A, B), CNY65(A, B), CNY66(A, B), CNY64(AYST, ABST, AGRST), CNY65(AYST, ABST, AGRST), CNY651(AGR, AYST, AGRST) 加强绝缘, 外部爬电距离 > 9.0mm, 绝缘穿透距离 ≥3.0mm, 通过热循环测试, 仅适用于海拔 5000 米及以下
产品标准和技术要求	GB 4943.1-2022
认证模式	产品型式试验+获证后监督

上述产品符合 CQC11-471543-2022 认证规则的要求, 特发此证。
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心

http://www.cqc.com.cn

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666