



Molded Photomodule Holders, Cuts, and Bends

| HOLDER | D | H | W | X | VIEW | TYPE |
|-------------|-------|-------|------|-------|------|--------|
| TE | 15.7 | 21.9 | 7.45 | 18.3 | Side | Holder |
| PM | 19.1 | 15.5 | 9.4 | 12 | Side | Holder |
| RF | 11.8 | 16 | 7.4 | 16 | Top | Holder |
| QJ | 11.8 | 20 | 7.4 | 20 | Top | Holder |
| UH | 9.25 | 13.2 | 7.4 | 9.6 | Side | Holder |
| XG | 11.4 | 22.6 | 7.4 | 19 | Side | Holder |
| YA | 14 | 12 | 7.4 | 12 | Top | Holder |
| WE | 14.25 | 22.6 | 7.45 | 19 | Side | Holder |
| JH | 9.2 | 13.2 | 7.4 | 9.6 | Side | Holder |
| JK | 9.2 | 13.2 | 7.4 | 9.6 | Side | Holder |
| JL | 9.2 | 13.2 | 7.4 | 9.6 | Side | Holder |
| LL | 14 | 7.2 | 7.4 | 7.2 | Top | Holder |
| ZC | 14 | 16 | 7.4 | 16 | Top | Holder |
| VI | 9.5 | 10.2 | 7.4 | 6.6 | Side | Holder |
| IV | 8.6 | 13.2 | 7.2 | 9.6 | Side | Holder |
| AY | 18.95 | 22.6 | 7.4 | 19 | Side | Holder |
| CZ | 9.65 | 6.8 | 6.8 | 6.8 | Top | Holder |
| VM1 | 9.5 | 10.2 | 7.4 | 6.6 | Side | Holder |
| CD | 16.3 | 22.45 | 6.8 | 19.35 | Side | Holder |
| MT | 23.1 | 13.1 | 12.2 | 9 | Side | Holder |
| CUT OR BEND | D | H | W | X | VIEW | TYPE |
| SA | 12.6 | 11.45 | 6 | 9.9 | - | Bend |
| SB | 9.65 | 20.8 | 6 | 6.95 | - | Bend |
| SC | 12.6 | 15.45 | 6 | 9.9 | - | Bend |
| SD | 9.65 | 16.2 | 6 | 6.95 | - | Bend |
| SK | 12.95 | 5.2 | 6 | 10.25 | - | Bend |
| SI | | 12.35 | 6 | 9.65 | - | Cut |
| SJ | 10.1 | 19.25 | 6 | 7.4 | - | Bend |
| SO | 10.1 | 9.6 | 6 | 7.4 | - | Bend |
| SP | 9 | 20.8 | 6 | 6.3 | - | Bend |
| SR | 17 | 10 | 6 | 14.3 | - | Bend |
| ST | 9.65 | 5 | 6 | 6.95 | - | Bend |
| SW | 9.65 | 7 | 6 | 6.95 | - | Bend |
| SL | 12.6 | 6.6 | 6 | 9.9 | - | Bend |
| DA | 9 | 21.6 | 6 | 6.3 | - | Bend |
| DE | - | 14.2 | 6 | 11.25 | - | Bend |
| DF | - | 12.25 | 6 | 9.55 | - | Bend |
| DG | - | 30.5 | 6 | 27.8 | - | Cut |
| DB | - | 18 | 6 | 15.3 | - | Cut |
| DI | 9.2 | 12.6 | 6 | 6.5 | - | Bend |
| DH | - | 7.2 | 6 | 6.3 | - | Bend |
| DK | 12.95 | 5 | 6 | 10.25 | - | Bend |
| DL | - | 12 | 6 | 9.3 | - | Bend |
| DM | - | 11.75 | 6 | 9.05 | - | Cut |

