



Cast Photomodule Holders, Cuts, and Bends

HOLDER	D	H	W	X	VIEW	TYPE
GL	20	20	12.5	20	Top	Holder
KA	11.25	13.8	11.5	9.75	Side	Holder
KD	11.25	13.8	11.5	9.75	Side	Holder
KS	11.25	13.8	11.5	9.75	Side	Holder
RF	16.65	16.4	12.5	16.4	Top	Holder
UU	20	8.5	12.5	8.5	Top	Holder
UQ	20	8.5	12.5	8.5	Top	Holder
WI	25.6	16.05	12.2	12	Side	Holder
XG	14.15	23.05	7.4	19	Side	Holder
CUT OR BEND	D	H	W	X	VIEW	TYPE
SB	15.4	14.8	10	12.3	-	Bend
SD	-	17.6	10	14.3	-	Cut
SE	-	17.6	10	14.3	-	Cut
SH	-	16	10	12.7	-	Cut
SK	-	21.1	10	17.8	-	Cut
SM	-	32.9	10	29.6	-	Cut
SP	17.4	15	10	14.3	-	Bend
SR	14.4	5.4	10	11.1	-	Bend
SA	-	16.6	10	13.3	-	Cut

