

# Optocoupler



## 产品认证证书

证书编号: CQC12001080777 发证日期: 2023年01月16日  
有效期至: 2028年01月15日

<b>委托人名称 及注册地址</b>	威旭半导体马来西亚有限公司 No. 1710-1Kawasan Perindustrian Krubong,75250 Melaka,马来西亚
<b>制造商名称 及注册地址</b>	威旭半导体马来西亚有限公司 No. 1710-1Kawasan Perindustrian Krubong,75250 Melaka,马来西亚
<b>生产企业名称 及生产地址</b>	威旭半导体马来西亚有限公司 No. 1710-1Kawasan Perindustrian Krubong,75250 Melaka,马来西亚
<b>产品名称和系列、 规格、型号</b>	光电耦合器 VOL628A-X (X=2,3,4),TCLT1600 :加强绝缘 ;适用于海拔 5000 米及以下 ;外部爬电距离 > 8.0mm ; 内部绝缘穿透距离 ≥ 0.4mm ; 通过热循环测试
<b>产品标准和技术要求</b>	GB 4943.1-2022
<b>认证模式</b>	产品型式试验+初次工厂检查+获证后监督

上述产品符合 CGC11-471543-2022 认证规则的要求, 特发此证。  
本证书为变更证书, 证书首次颁发日期: 2012年09月20日  
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 ( www.cnca.gov.cn ) 查验证书信息



签发: 



### 中国质量认证中心



http://www.cqc.com.cn 中国·北京·南四环西路188号9区 100070 电话: +86 10 83886666

C 0544749

Revision: 21-Feb-2023

1

Document Number: 85384

For technical questions, contact: [optocoupleranswers@vishay.com](mailto:optocoupleranswers@vishay.com)

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT [www.vishay.com/doc?91000](http://www.vishay.com/doc?91000)

 <b>CERTIFICATE OF PRODUCT CERTIFICATION</b>	
<b>CERTIFICATE NO.:</b> CQC12001080777	<b>Valid from:</b> Jan.16,2023 <b>Valid until:</b> Jan.15,2028
<b>NAME AND REGISTERED ADDRESS OF THE APPLICANT</b>	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1Kawasan Perindustrian Krubong,75250 Melaka,Malaysia
<b>NAME AND REGISTERED ADDRESS OF THE MANUFACTURER</b>	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1Kawasan Perindustrian Krubong,75250 Melaka,Malaysia
<b>NAME AND LOCATION OF THE FACTORY</b>	Vishay Semiconductor Malaysia Sdn Bhd No. 1710-1Kawasan Perindustrian Krubong,75250 Melaka,Malaysia
<b>PRODUCT NAME, MODEL AND SPECIFICATION</b>	Opto couplers VOL628A-X (X=2,3,4),TCLT1600 : Reinforced Insulation; Altitude up to 5000m ; ext.cr> 8.0mm ; dti≥0.4mm ; Thermal Cycling test passd
<b>THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS</b>	GB 4943.1-2022
<b>TYPE OF CERTIFICATION SCHEMES</b>	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection
<p>This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022. Date of original issued: Sep.20,2012 The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.</p>	
<p>The certificate information is available through the QR code below or CNCA's website: <a href="http://www.cnca.gov.cn">www.cnca.gov.cn</a></p>	
	<p>SIGNATURE: </p>  <p><b>CHINA QUALITY CERTIFICATION CENTRE</b></p> 
<p><a href="http://www.cqc.com.cn">http://www.cqc.com.cn</a>      Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China      Tel: +86 10 83886666</p>	
<p><b>C 0544749</b></p>	