

Optocoupler



PRODUCT CERTIFICATE

No.: CQC13001088687

NAME AND ADDRESS OF THE APPLICANT

Vishay Semiconductor Malaysia Sdn Bhd
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

NAME AND ADDRESS OF THE MANUFACTURER

Vishay Semiconductor Malaysia Sdn Bhd
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

NAME AND ADDRESS OF THE FACTORY

Vishay Semiconductor Malaysia Sdn Bhd (V002589)
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

NAME, MODEL AND SPECIFICATION

OPTO COUPLERS

Refer to annex, Reinforced Insulation, Altitude up to 2000m, ext.cr>5.5mm, dt \geq 0.4mm, Thermal Cycling test passd

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB4943.1-2011

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2015 .

Date of issue: May.20,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Feb.19,2013

President:


Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nanshuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0082698



产品认证证书

证书编号: CQC13001088687

申请人名称及地址

威旭半导体马来西亚有限公司
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚

制造商名称及地址

威旭半导体马来西亚有限公司
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚

生产企业名称及地址

威旭半导体马来西亚有限公司 (V002589)
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka 马来西亚

产品名称和系列、规格、型号

光电耦合器

见附件, 加强绝缘, 外部爬电距离 $\geq 5.5\text{mm}$, 绝缘穿透距离 $\geq 0.4\text{mm}$, 通过热循环测试, 仅适用于海拔2000米及以下

产品标准和技术要求

GB4943.1-2011

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471543-2015 认证规则的要求, 特发此证。

发证日期: 2016年05月20日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2013年02月19日

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0082698



产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC13001088687

纸号: 82698

SFH690AT、SFH690ABT、SFH690BT、SFH690CT、SFH690DT、SFH690AXXXXT、SFH690ABXXXT、
SFH690BXXXT、SFH690CXXXT、SFH690DXXXT、SFH1690(A, B, C, AB)T-XXXX

(注: 型号中的变量“x”仅代表包装形式和 VDE 局部放电的代号, 可以是空白, 字母 A-Z 或者数字 1-9 的组合)

加强绝缘, 外部爬电距离 > 5.5mm, 绝缘穿透距离 ≥ 0.4mm, 通过热循环测试, 仅适用于海拔 2000 米及以下

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>