

## Optocoupler



# 产品认证证书

证书编号: CQC14001105201

### 申请人名称及地址

威旭半导体马来西亚有限公司  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

### 制造商名称及地址

威旭半导体马来西亚有限公司  
No. 1710-1, Kawasan Perindustrian Krubong 75250 Melaka 马来西亚

### 生产企业名称及地址

亿光电子(中国)有限公司 (V008546)  
江苏省吴江经济开发区运西分区中山北路2135号

### 产品名称和系列、规格、型号

光电耦合器

见附件: 规格: 加强绝缘, 外部爬电距离 > 8mm, 内部绝缘穿透距离 > 0.4mm, 通过10次热循环, (仅适用于海拔5000米及以下)

### 产品标准和技术要求

GB4943.1-2011

### 认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471543-2012认证规则的要求, 特发此证。

发证日期: 2014年01月26日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路188号9区100070

http://www.cqc.com.cn

C 0056867



## PRODUCT CERTIFICATE

No.: CQC14001105201

### NAME AND ADDRESS OF THE APPLICANT

Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia

### NAME AND ADDRESS OF THE MANUFACTURER

Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong 75250 MelakaMalaysia

### NAME AND ADDRESS OF THE FACTORY

EVERLIGHT ELECTRONICS(CHINA)CO.,LTD. (V008546)  
No.2135 Zhong Shan North Rd.,Wujiang Economy Development Zone(Yun Xi Area)Wujiang City, Jiang  
Su Pre, China

### NAME, MODEL AND SPECIFICATION

Optocoupler

See appendix: reinforced insulation, distance through insulation $\geq$ 0.4mm, external creepage distance $>$ 8.0mm, thermal cycling test, Altitude up to 5000m

### THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB4943.1-2011

### CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2012.

Date of issue: Jan.26,2014

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President:



Wang Kejiao



## CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R. China  
<http://www.cqc.com.cn>

c 0056867



# 产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC14001105201

纸号: 56867

4N25、4N26、4N27、4N28、4N35、4N36、4N37、4N38、CNY17-1、CNY17-2、CNY17-3、  
CNY17-4、4N25V、4N35V、4N38A、CNY17G-1、CNY17G-2、CNY17G-3、CNY17G-4、CNY75A、  
CNY75B、CNY75C、CQY80N、K233P、TCDT1100、TCDT1101、TCDT1102、TCDT1103、TCDT1110、  
TCDT1120、TCDT1122、TCDT1123、TCDT1124、4N25GV、4N35GV、CNY75GA、CNY75GB、  
CNY75GC、CQY80NG、K233PG、TCDT1100G、TCDT1101G、TCDT1102G、TCDT1103G、TCDT1110G、  
TCDT1120G、TCDT1122G、TCDT1123G、TCDT1124G

注: 此附录与证书同时使用时有效。

主任: \_\_\_\_\_



## 中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>