




PowerPAK® 8 x 8LR Carrier Tape (HVM)



DIM.	MILLIMETERS
A ₀	8.66 ± 0.10
B ₀	10.77 ± 0.10
K ₀	2.20 ± 0.10

ECN: S24-0003-Rev. A, 08-Jan-2024
DWG: 93-5359-X

Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2 mm
- (2) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole
- Dimensions are in mm
- A₀ and B₀ are measured on a plane at a distance “R” above the bottom of the pocket
- Material PS + C
- Refer to T115617BT revision 0