

FP/C6 SPEC CODES

STYLE	STD or NON- STD	SPEC	DESCRIPTION	TOL	A5 R36	B8 B8	BA B14	C2 N/A	C3 C3	CB N/A	E8	G1	M6 N/A	M8 N/A	27 N/A	N2	NB	N3	NC			LB
			PACKAGE CODES FROM DPS-327																	R20	K04	L05
FP01/2	STD	5605	1/2W, FP, 5 BAND CC / 4 BAND CC	1 / 2, 5, 10	YES	YES	YES		YES												YES	YES
	STD	5610	1/2W, FP, TYPE MARKED	1, 2, 5, 10	YES	YES			YES				YES		YES							
FP1/2P	STD	5555	1/2W, FP, PULSE, TYPE MARKED	1, 2, 5	YES	YES			YES				YES		YES							
	N-STD	5556	1W, FP, LUCENT PERMARK KS23040	1									YES		YES							
	N-STD	5557	1/2W, FP, PULSE, LOCKHEED	1, 2, 5	YES	YES																
FP0001	STD	6200	4 BAND CC, 032 LEAD	2, 5, 10	YES	YES			YES													
	STD	6201	1W, FP, 5BAND CC, 032 LEAD	1	YES	YES			YES												YES	
FP001P	N-STD	6204	1W, FP, PULSE, TYPE MARK, 032 LEAD, LUCENT	.5, 1, 2, 5		YES			YES													
	STD	6206	1W, FP, PULSE, TYPE MARK, 032 LEAD	1, 2, 5		YES			YES							YES						
FP001D	STD	6276	1W, FP, TYPE MARKED, 032 LEAD	1, 2				YES								YES	YES					
C00006	STD	6301	1W, EPOXY, 5 BAND CC, 040 LEAD	1		YES			YES													
	STD	6302	1W, EPOXY, 4 BAND CC, 040 LEAD	2, 5, 10					YES													
	STD	6330	1W, EPOXY, 5 BAND CC, 032 LEAD	1					YES													
	STD	6331	1W, EPOXY, 4 BAND CC, 032 LEAD	2, 5, 10					YES													
FP0032	STD	6601	1W, FP, 5 BAND CC, 040 LEAD	1		YES			YES													
	STD	6602	1W, FP, 4 BAND CC, 040 LEAD	2, 5, 10	YES	YES			YES							YES			YES			
	STD	6603	1W, FP, 4 BAND CC, 032 LEAD	2, 5		YES		YES	YES							YES						
	STD	6606	1W, FP, 5 BAND CC, 032 LEAD	1		YES										YES						
	N-STD	6608	1W, FP, TYPE MARKED, 040 LEAD	1, 2, 5	YES	YES			YES													
	N-STD	6609	1W, FP, 5BAND, BAND 5 WHITE, O40 LEAD	2, 5	YES				YES													
FP0069	STD	7500	2W, FP, TYPE MARKED	1, 2, 5, 10	YES	YES			YES	YES				YES	YES		YES					
	N-STD	7510	2W, FP, LUCENT PERMARK 20289	1, 2, 5, 10		YES							YES		YES							
	N-STD	7515	2W, FP, TYPE MARKED FOR IBM	1, 2, 5		YES								YES								
	STD	7536	2W, FP, 4BAND CC	2, 5, 10	YES	YES			YES													
	STD	7538	2W, FP, 5BAND CC	1	YES									YES								
	N-STD	7542	2W, FP, PERMARK WITH IBM PART NUMBER	1, 2, 5		YES								YES								
FP069P	STD	7532	2W, FP, PULSE, TYPE MARKED	1, 2, 5, 10	YES	YES			YES				YES		YES							
	N-STD	7533	2W, FP, PULSE, LUCENT PERMARK KS23037	1									YES		YES							
	N-STD	9911	2W, FP, PULSE, TYPE MARKED, 24 HR B/I	1		YES																
FP0042	STD	9201	2W, FP, 5BAND CC, 045 LEAD	1	YES	YES			YES								YES					
	STD	9202	2W, FP, 4BAND CC, 045 LEAD	2, 5, 10	YES	YES			YES								YES					
	STD	9203	2W, FP, 4BAND CC, 032 LEAD	2, 5, 10	YES	YES	YES	YES	YES								YES		YES			
	STD	9207	2W, FP, 5BAND CC, 032 LEAD	1													YES					
	N-STD	9209	2W, FP, HOT SOLDER DIPPED LEAD SPECIAL	1, 2, 5, 10					YES													
FP42TX	STD	9913	2W, FP, TYPE MARKED, 24 HOUR BI, NOT MIL	2, 5		YES			YES													
FP0002	N-STD	9250	2W, FP, LUCENT PERMARK KS20289L3	1, 2, 5, 10		YES			YES						YES							

[illegible]