



Fixed Resistors Packaging

SERIES	MINIMUM QUANTITY PER			
	TAPE AND REEL		BAG	OTHER
	REEL	AMMO-PACK		
<b>MSP</b>			Only Techno B	Tube
MSP1	500	-	x 100	70
MSP2	500	-	x 100	50
MSP3 only Techno B	-	-	x 100	40
<b>RTO</b>				Tube
RTO20 - RTO50	-	-	-	50
<b>RCH</b>				
RCH 5	-	-	25	-
RCH 10	-	-	25	-
RCH 25	-	-	25	-
RCH 50	-	-	25	-
<b>RPH</b>				Box
RPH 100	-	-	-	5
<b>RTOP</b>				Box
RTOP 200	-	-	-	10
RTOP 100	-	-	-	10
DRTOP 100	-	-	-	10
DRTOP 50	-	-	-	10
TRTOP 40	-	-	-	10
TRTOP 30	-	-	-	10
QRTOP 35	-	-	-	10
QRTOP 20	-	-	-	10
<b>RPS</b>				Box
RPS 250 - 500	-	-	-	15
<b>RWM</b>				Box
RWM 6 x 34	-	-	-	50
RWM 8 x 34	-	-	-	50
RWM 8 x 45	-	-	-	50
RWM 10 x 45	-	-	-	50
RWM 10 x 64	-	-	-	50
RWM 10 x 65	-	-	-	50
<b>RLP</b>				
RLP 1	1000	500	100	-
RLP 2	1000	500	100	-
RLP 3	1000	500	-	20 blister
RLP 6	-	-	-	50 box
RLP 10	-	-	-	50 box
<b>RMB</b>				
RMB 0.75	1000	500	100	-
RMB 1.5	1000	500	100	-
RMB 3	1000	500	50	-
<b>RMBS</b>				
RMBS 05	1000	500	100	-
RMBS 1	1000	500	100	-
RMBS 2	1000	500	50	-
<b>BSI</b>				Box
58 BSI	5000	2000	-	-
63 BSI	3000	1000	-	-
68 BSI	1250	400	-	-
516 BSI	1250	400	-	-
523 BSI	1250	400	-	-
923 BSI	500	250	-	-
932 BSI	-	-	-	30
947 BSI	-	-	-	30
<b>SG</b>				Case
SG3	1500	-	-	-
SG4	1250	-	-	-

SERIES	MINIMUM QUANTITY PER			
	TAPE AND REEL		BAG	OTHER
	REEL	AMMO-PACK		
<b>RH - SH</b>				
RH 5- SH 5	-	-	10	-
RH 10- SH 10	-	-	10	-
RH 25- SH 25	-	-	10	-
RH 50- SH 50	-	-	10	-

SERIES	BOX COLLARS			
	TAPE AND REEL		B	CS
	BAG OR BOX	AN AND FASTON		
<b>RW</b>				
RW 8 x 34	25	-	-	-
RW 10 x 50	25	-	-	-
RW 13 x 70	-	40	50	50
RW 16 x 94	-	30	30	-
RW 20 x 117	-	20	20	-
RWST 25 x 138	-	6	6	4
RWST 25 x 168	-	6	6	4
RWST 30 x 250	-	6	6	4
RWST 40 x 370	-	2	-	2
RWST 50 x 373	-	1	-	1
<b>RSO</b>				
RSO 25 x 138	-	3/6	-	2/4
RSO 25 x 168	-	3/6	-	2/4
RSO 30 x 250	-	3/6 <sup>(1)</sup>	-	2/4 <sup>(1)</sup>
RSO 40 x 370	-	1	-	1
RSO 50 x 373	-	1	-	1
<b>RSSD</b>				
RSSD 8 x 34	50	-	-	-
RSSD 10 x 50	25	-	-	-
RSSD 13 x 70	-	30	-	-
RSSD 16 x 94	-	30	-	-
RSSD 20 x 117	-	20	-	-
RSSD 25 x 138	-	6	-	4
RSSD 25 x 168	-	6	-	4
RSSD 30 x 250	-	6	-	4
RSSD 40 x 370	-	2	-	2
RSSD 60 x 373	-	1	-	1
<b>RT</b>	Box	Box		
RT 12	1	10		
RT 25	1	10		
RT 55	1	-		
RT 100	1	-		
RT 230	1	-		
RT 500	1	-		
<b>RA</b>				
RA 13 x 70		10	10	-
RA 16 x 94		10	10	-
RA 20 x 117		10	10	-
RA 25 x 138		4	4	-
RA 25 x 168		4	4	-
RA 30 x 250		3	3	-

Note

(1) Depend of ohmic value



SERIES	TYPE	PACKAGING		
		BAG	AMMO-PACK	TAPE AND REEL
RCMM	02	100	500	1000
	05	100	500	-
	1	500	500	-
RCMS	02	100	500	1000
	05	100	500	-
	1	500	500	-
RCMX	02	100	500	1000
	05	100	500	-
	1	500	500	-
RCMA	02	10/100	500	-
	05	10/100	500	-
	08	10/50	-	-
	1	10/50	-	-
	2	50	-	-
	4	50	-	-
RCME	All types	10/100	500	-
RCMT	01	10/100	-	-
	02	10/100	500	-
	05	10/100	500	-
	08	10/50	-	-
	1	10/50	-	-
	2	50	-	-
	4	50	-	-

SERIES	TYPE	PACKAGING
		TUBE
LTO	30	50
	50	50
	100	30

SERIES	TYPE	PACKAGING
		BOX
RPS	250	15
	500	15
LPS	300	15
	600	15
	800	15
	1100	15

SERIES	TYPE	PACKAGING	
		TUBE	TAPE AND REEL
D2TO	20	50	500
	35	50	500

SERIES	TYPE	PACKAGING			
		BLISTER	AMMO-PACK	BOX	TAPE AND REEL
HTS	58/63	25	500	-	-
	68	20	500	-	-
	932/947	-	-	30	-
	523/547	-	-	30	-
	972/9100	-	-	40	-
	729/747	-	-	40	-
HPS	58/63	20	500	-	-
	68	20	400	-	-
	523	-	-	30	500
	923/932/947	-	-	30	-