



ENVIRONMENTAL AND PACKAGE TESTING DATA FOR D²PAK (TO-263) (HVM)					
STRESS	SAMPLE SIZE	DEVICE HR./CYC	CONDITION	TOTAL FAILS	FAIL PERCENTAGE
BOND INT	20	10 000	200 °C + N2	0	0.00
HAST	220	22 000	130 °C, 85 % RH	0	0.00
Pressure Pot	220	21 120	121°, 15 PSIG	0	0.00
Temp. Cycle	220	211 500	-55 °C to 150 °C	0	0.00