



## CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC12001067600

Valid from: Aug.21,2024

Valid until:Aug.20,2029

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** VISHAY CAPACITORS BELGIUM NV  
Kwadestraat 151a, bus 12, 8800 Roeselare,Belgium

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** VISHAY CAPACITORS BELGIUM NV  
Kwadestraat 151a, bus 12, 8800 Roeselare,Belgium

**NAME AND LOCATION OF THE FACTORY** Vishay Electronica Portugal, LDA  
Rua Magalhaes Lima 256, 4760-363 Vila Nova Famalicao , Portugal

**PRODUCT NAME, MODEL AND SPECIFICATION** Fixed capacitors for electromagnetic interference suppression and connection to the supply mains  
see appendix

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB/T 6346.14-2023

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471115-2023.

Date of original issued: Mar.13,2012

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
<http://www.cqc.com.cn>



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC12001067600

page 1 of 3

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

型号规格	电容量	偏差	外形尺寸			薄膜尺寸			体积
			L(mm)	H(mm)	W(mm)	Max L (mm)	Max H (mm)	Max W (mm)	
F339X1 330Vac X1 0.001µF ~2.2µF 55/110/ 56/B	nF								
	1	M,K	10	9	4	7.9	6	2.1	360
	1.2	K	10	9	4	7.9	6.2	2.3	360
	1.5	M,K	10	9	4	7.9	6.1	2.2	360
	1.8	K	10	9	4	7.9	6.3	2.4	360
	2.2	M,K	10	9	4	7.9	6.5	2.7	360
	2.7	K	10	9	4	7.9	6.9	3.1	360
	3.3	M,K	10	10.5	5	7.9	7.3	3.3	525
	3.9	K	10	10.5	5	7.9	7.6	3.8	525
	4.7	M,K	10	11.5	6	7.9	8.1	4.3	690
	5.6	K	10	11.5	6	7.9	8.5	4.8	690
	1	M,K	12.5	10	4	9.9	6.8	2.1	500
	1.2	K	12.5	10	4	9.9	6.8	2.1	500
	1.5	M,K	12.5	10	4	9.9	7	2.3	500
	1.8	K	12.5	10	4	9.9	7.2	2.6	500
	2.2	M,K	12.5	10	4	9.9	6.8	2.2	500
	2.7	K	12.5	10	4	9.9	6.8	2.2	500
	3.3	M,K	12.5	10	4	9.9	7.1	2.5	500
	3.9	K	12.5	10	4	9.9	7.4	2.8	500
	4.7	M,K	12.5	10	4	9.9	6.9	2.2	500
	5.6	K	12.5	10	4	9.9	7	2.5	500
	6.8	M,K	12.5	10	4	9.9	7.3	2.7	500
	8.2	K	12.5	10	4	9.9	6.5	2	500
	10	M,K	12.5	10	4	9.9	6.5	2	500
	12	K	12.5	10	4	9.9	6.8	2.2	500
	15	M,K	12.5	10	4	9.9	7.1	2.5	500
	18	K	12.5	11	5	9.9	7.4	2.9	688
	22	M,K	12.5	11	5	9.9	7.8	3.3	688
	27	K	12.5	12	6	9.9	8.3	3.8	900
	33	M,K	12.5	12	6	9.9	8.7	4.3	900
	10	M,K	17.5	11	5	14.7	7.9	3.2	963
	12	K	17.5	11	5	14.7	8.2	3.4	963
	15	M,K	17.5	11	5	14.7	8.4	3.6	963
22	M,K	17.5	11	5	14.7	7.2	2.5	963	
33	M,K	17.5	11	5	14.7	7.9	3.2	963	



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
http://www.cqc.com.cn



**CERTIFICATE OF PRODUCT CERTIFICATION**

CERTIFICATE NO. : CQC12001067600

page2of3

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

39	K	17.5	11	5	14.7	7.7	3	963
47	M,K	17.5	11	5	14.7	8	3.3	963
56	K	17.5	12	6	14.7	8.4	3.7	1260
68	M,K	17.5	12	6	14.7	8.8	4.2	1260
82	K	17.5	13.5	7	14.7	9.4	4.7	1654
100	M,K	17.5	13.5	7	14.7	10	5.4	1654
120	K	17.5	15	8.5	14.7	10.7	6	2231
150	M,K	17.5	15	8.5	14.7	11.5	6.9	2231
180	K	17.5	16.5	10	14.7	12.3	7.7	2888
220	M,K	17.5	16.5	10	14.7	13.2	8.6	2888
100	M,K	26	15.5	6	22	10.9	3	2418
120	K	26	15.5	6	22	11.1	3.3	2418
150	M,K	26	15.5	6	22	11.5	3.8	2418
180	K	26	16.5	7	22	12.1	4.3	3003
220	M,K	26	16.5	7	22	12.7	4.9	3003
270	K	26	18	8.5	22	13.4	5.6	3978
330	M,K	26	18	8.5	22	14.2	6.4	3978
390	K	26	19.5	10	22	15	7.2	5070
470	M	26	19.5	10	22	15.3	7.6	5070
470	K	26	22	12	22	15.9	8.2	6864
560	K	26	22	12	22	16.8	9.1	6864
680	M	26	22	12	22	17.3	9.6	6864
680	K	26.5	22.5	12.5	22	18	10.2	7453
820	M	26.5	22.5	12.5	22	18.5	10.8	7453
220	M,K	31.5	19	9	27	13.4	5.6	5387
270	K	31.5	19	9	27	14.2	6.4	5387
330	M,K	31.5	19	9	27	13.1	5.3	5387
390	K	31.5	19	9	27	13.8	6	5387
470	M	31.5	19	9	27	14.1	6.3	5387
470	K	31	21	11	27	14.5	6.8	7161
560	K	31	21	11	27	15.3	7.6	7161
680	M	31	21	11	27	15.7	8	7161
680	K	31	23	13	27	16.4	8.6	9269
820	K	31	23	13	27	17.5	9.7	9269
1000	M	31	23	13	27	18	10.3	9269
1000	K	31.5	25	15	27	18.8	11	11813
1200	M	31.5	25	15	27	20	12.4	11813



**中国质量认证中心**  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
<http://www.cqc.com.cn>



**CERTIFICATE OF PRODUCT CERTIFICATION**


CERTIFICATE NO. : CQC12001067600

page 3 of 3

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

1500	M,K	31.5	28	18	27	21.8	14.2	15876
1800	K	31	31	21	27	23.5	15.9	20181
2200	M,K	31	31	21	27	25.5	18	20181



**中国质量认证中心**  
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
<http://www.cqc.com.cn>