




SIDBRAZE: 20-LEAD

Meets MIL-STD-1835, D8, Configuration C



| Dim | MILLIMETERS | | INCHES | |
|----------------------|-------------|-------|-----------|-------|
| | Min | Max | Min | Max |
| A | 2.67 | 4.45 | 0.105 | 0.175 |
| b | 0.38 | 0.53 | 0.015 | 0.021 |
| b₂ | 1.14 | 1.65 | 0.045 | 0.065 |
| c | 0.20 | 0.30 | 0.008 | 0.012 |
| D | 24.89 | 26.16 | 0.980 | 1.030 |
| E | 7.11 | 7.87 | 0.280 | 0.310 |
| e | 2.54 BSC | | 0.100 BSC | |
| e_A | 7.62 BSC | | 0.300 BSC | |
| L | 3.18 | 4.45 | 0.125 | 0.175 |
| Q | 0.64 | 1.40 | 0.025 | 0.055 |
| S₂ | 0.25 | – | 0.010 | – |
| S₁ | 0.13 | – | 0.005 | – |

ECN: S-03946—Rev. D, 09-Jul-01
DWG: 5309