




**FLAT PACK: 16-LEAD**



Dim	MILLIMETERS		INCHES	
	Min	Max	Min	Max
A	1.78	2.29	0.070	0.090
b	0.38	0.48	0.015	0.019
c	0.10	0.18	0.004	0.007
D	9.91	10.41	0.390	0.410
E	6.60	7.11	0.260	0.280
E <sub>2</sub>	4.57	5.08	0.180	0.200
E <sub>3</sub>	0.76	1.27	0.030	0.050
e	1.27 BSC		0.050 BSC	
H	22.35	23.88	0.880	0.940
L	7.62	8.89	0.300	0.350
Q	0.25	0.51	0.010	0.020
S	–	1.02	–	0.040
S <sub>1</sub>	0.13	–	0.005	–

ECN: S-03946—Rev. C, 09-Jul-01  
DWG: 5430