



Bent Leads:
D = 10.1 mm, H = 9.6 mm, W = 5 mm, X = 7.4 mm

AVAILABLE FOR

- Minicast




LINKS TO ADDITIONAL RESOURCES



NAME	LENS AXIS (X)	VIEW	TYPE	HEIGHT (H)	WIDTH (W)	DEPTH (D)
SO1	7.4	-	Bend	9.6	5	10.1



MECHANICAL DIMENSIONS in millimeters




Drawing-No.: 6.550-5281.06-4

Issue: 2; 12.03.10

21509

PACKAGING DIMENSIONS in millimeters



Drawing-No.: 9.700-5309.0-4
Rev. 2; Date: 26.10.07
20440

ORDERING INFORMATION

T S O P

d d d

d d

S O 1

Product series
(2 or 3 digits)

Frequency

Holder type


Note

- d = "digit", please consult the list of available series on the previous page to create a valid part number

Example: TSOP39238SO1

PACKING QUANTITY

- 105 pieces per tube
- 30 tubes per carton

OUTER PACKAGING
CARTON BOX DIMENSIONS in millimeters


KINDS OF CARTON BOX	THICKNESS	WIDTH	LENGTH
Packaging plastic tubes (normal / auxiliary devices)	80	150	600
Packaging plastic trays (devices with metal holders)	120	290	490
Big box (bulk packaging)	150	180	400
Secondary box (taping in reels)	400	310	410
Ammo-box (zigzag taping)	50	130	350